




Specifications:

Items	Performance
Type:	high voltage trigger
Input:	300 volts
Output:	10000 volts
DCR (N1):	0.16Ω max.
DCR (N2):	420Ω±20%
N1:	(1- 2) 3-4 IVC ±20% 1KHz 0.3V
N2:	(4 -3) 28 IVC ±20% 1KHz 0.3V
Wire:	(N1): polyurethane enameled copper; 0.23mm (2UEW) 11 1/4 TS
Wire :	(N2): polyurethane enameled copper wire; 0.06mm (USTC) 1500TS
Bobbin:	phenolic molding powder T375J 94V-0 E59481 (S)
Core:	ferrite core T2F TH6x8 or equivalent
Insulating tape:	polyester film insulating tape no. 500 E74186 (S)
Wax:	fully refined paraffin wax 135°/140° F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[422-2310](#)