


| *PANDUIT<br>PART<br>NUMBER | A<br>IN<br>(mm) | B<br>IN<br>(mm)          | T<br>IN<br>(mm)        | WEIGHT<br>LBS / 100 FT<br>(g) |
|----------------------------|-----------------|--------------------------|------------------------|-------------------------------|
| T12T                       | .125<br>(3.2)   | .218±.047<br>(5.5±1.2)   | .020±.006<br>(0.5±0.2) | 0.6<br>(272.2)                |
| T19T                       | .188<br>(4.8)   | .250±.047<br>(6.4±1.2)   | .030±.008<br>(0.8±0.2) | 1.3<br>(589.7)                |
| T25T                       | .250<br>(6.4)   | .375±.047<br>(9.5±1.2)   | .030±.008<br>(0.8±0.2) | 1.9<br>(861.8)                |
| T38T                       | .375<br>(9.5)   | .437±.047<br>(11.1±1.2)  | .030±.010<br>(0.8±0.3) | 2.8<br>(1270.0)               |
| T50T                       | .500<br>(12.7)  | .500±.047<br>(12.7±1.2)  | .030±.016<br>(0.8±0.4) | 4.1<br>(1859.7)               |
| T62T                       | .625<br>(15.9)  | .625±.047<br>(15.9±1.2)  | .030±.020<br>(0.8±0.5) | 5.0<br>(2267.9)               |
| T75T                       | .750<br>(19.1)  | .875±.047<br>(22.2±1.2)  | .030±.020<br>(0.8±0.5) | 6.3<br>(2857.6)               |
| T100T                      | 1.000<br>(25.4) | 1.125±.047<br>(28.6±1.2) | .040±.020<br>(1.0±0.5) | 11.4<br>(5158)                |



- NOTES:
- \* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS, PACKAGE SIZE AND PART COLOR
  - 2) FOR ROLL SIZES LARGER THAN 10 FT., SPLICING MAY OCCUR.
  - 3) REVERSE CUT

[illegible]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T62T-Q](#) [T75T-X](#)