

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190700123](#)
Status: **Active**
Description: InsulKrimp™ Ring Tongue Terminal for 10-12 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)


General
Product Family Ring and Spade Terminals
Series [19070](#)
Mil-Spec N/A
Product Name InsulKrimp™
Type Ring

Physical
Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation PVC
Material - Plating Mating Tin
Packaging Type Bag
Stud Size 10 (M5)
Wire Insulation Diameter 6.40mm (.250") max.
Wire Size AWG 10, 12
Wire Size mm² 3.30 - 5.00

Electrical
CSA LR18689
UL E32244

Material Info
Old Part Number C-228-10X

Reference - Drawing Numbers
Product Specification PS-19902-009
Sales Drawing CCD20101



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19070Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640011500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION