

RG59B Coaxial Cable, F Male / Male, 3.0ft

Features for this product

- 75 Ohm video signal transmission
- Machined gold plated contacts of Type F connector reduce signal loss
- Molded strain relief enhances durability
- RG59B/U solid center conductor minimizes cable attenuation
- Available from stock in 8 lengths ranging from 1 to 100 feet



This series of high quality 75 Ohm RG59B/U cable assemblies is ideal for applications where high quality video signal transmission is needed. Our Type F connectors feature machined gold plated center contacts for minimal signal loss. In addition our molded strain relief provides superior durability. We offer this series in 8 standard lengths from 1 to 100 feet stocked and ready for immediate delivery.

Details for this Coaxial product

L-com Item #	CCF59B-3
Manufacturer	L-com
UPC #	822335007536
RoHS Status	Not Compliant At This Time



Item #	Description	NOMINAL ATTENUATION		
RG59B/U 75 Ohm Impedance	- Center Conductor: 22 AWG solid bare copper covered steel - Shielding: Bare copper braid (95% coverage) - Insulation: Polyethylene - Jacket: Black PVC - Operating Temperature: -40°C - +80°C	MHz	db/100 ft	db/100m
		50	2.4	7.9
		100	3.4	11.1
		200	4.9	16.1
		400	7.0	23.0
		1000	12.0	39.3

✓ RG59B/U - 75 Ohm Coaxial Cables with Inline BNC Plug to BNC Jack

CC59B-MF-1	RG59B Cable, BNC Male / Female Bulkhead, 1.0 ft
CC59B-MF-3	RG59B Cable, BNC Male / Female Bulkhead, 3.0 ft
CC59B-MF-6	RG59B Cable, BNC Male / Female Bulkhead, 6.0 ft
CC59B-MF-10	RG59B Cable, BNC Male / Female Bulkhead, 10.0 ft
CC59B-MF-15	RG59B Cable, BNC Male / Female Bulkhead, 15.0 ft
CC59B-MF-25	RG59B Cable, BNC Male / Female Bulkhead, 25.0 ft
CC59B-MF-50	RG59B Cable, BNC Male / Female Bulkhead, 50.0 ft

✓ RG59B/U - 75 Ohm Coaxial Cables with One Inline BNC to One Right Angle BNC Plug

CC59B-1HR	RG59B Cable, BNC Male / 90° Male, 1.0 ft
CC59B-1.5HR	RG59B Cable, BNC Male / 90° Male, 1.5 ft
CC59B-2HR	RG59B Cable, BNC Male / 90° Male, 2.0 ft
CC59B-2.5HR	RG59B Cable, BNC Male / 90° Male, 2.5 ft
CC59B-3HR	RG59B Cable, BNC Male / 90° Male, 3.0 ft
CC59B-4HR	RG59B Cable, BNC Male / 90° Male, 4.0 ft
CC59B-5HR	RG59B Cable, BNC Male / 90° Male, 5.0 ft
CC59B-7.5HR	RG59B Cable, BNC Male / 90° Male, 7.5 ft
CC59B-10HR	RG59B Cable, BNC Male / 90° Male, 10.0 ft

✓ RG59B/U - 75 Ohm Coaxial Cables with Two Right Angle BNC Plugs

CC59B-1HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.0 ft
CC59B-1.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.5 ft
CC59B-2HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.0 ft
CC59B-2.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.5 ft
CC59B-3HR2	RG59B Cable, BNC 90° Male / 90° Male, 3.0 ft
CC59B-4HR2	RG59B Cable, BNC 90° Male / 90° Male, 4.0 ft
CC59B-5HR2	RG59B Cable, BNC 90° Male / 90° Male, 5.0 ft
CC59B-7.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 7.5 ft
CC59B-10HR2	RG59B Cable, BNC 90° Male / 90° Male, 10.0 ft

RG59B/U - 75 Ohm Coaxial Cables with Two Inline Molded Type F Plugs

CCF59B-1	RG59B Cable, Type F Male / Male, 1.0 ft
CCF59B-3	RG59B Cable, Type F Male / Male, 3.0 ft
CCF59B-6	RG59B Cable, Type F Male / Male, 6.0 ft
CCF59B-9	RG59B Cable, Type F Male / Male, 9.0 ft
CCF59B-12	RG59B Cable, Type F Male / Male, 12.0 ft
CCF59B-25	RG59B Cable, Type F Male / Male, 25.0 ft
CCF59B-50	RG59B Cable, Type F Male / Male, 50.0 ft
CCF59B-100	RG59B Cable, Type F Male / Male, 100.0 ft

RG6/U - 75 Ohm Coaxial Cables with Two Inline Type F Plugs

This series features low loss RG6 coaxial cable popular in transmission of television signal over cable. Features include: gold flash on connector surfaces, molded strain relief on the connector for superior protection and a captivated gold plated center conductor, not the cable's center conductor typically found in lower quality assemblies.

RG6/U 75 Ohm Impedance	- Center Conductor: 18 AWG solid bare copper covered steel - Shielding: Inner foil (100% coverage); Outer, copper braid (60% coverage) - Insulation: Foam Polyethylene - Jacket: Black PVC - Operating Temperature: -40°C - +80°C	NOMINAL ATTENUATION		
		MHz	db/100 ft	db/100m
		50	1.5	4.9
		100	2.1	6.9
		200	3.1	10.2
		400	4.5	14.8
		1000	7.3	23.9

CCF6-1	RG6 Cable, Type F Male / Male, 1.0 ft
CCF6-3	RG6 Cable, Type F Male / Male, 3.0 ft
CCF6-6	RG6 Cable, Type F Male / Male, 6.0 ft
CCF6-9	RG6 Cable, Type F Male / Male, 9.0 ft
CCF6-12	RG6 Cable, Type F Male / Male, 12.0 ft
CCF6-25	RG6 Cable, Type F Male / Male, 25.0 ft
CCF6-50	RG6 Cable, Type F Male / Male, 50.0 ft
CCF6-100	RG6 Cable, Type F Male / Male, 100.0 ft

✓ RG6/U - 75 Ohm Coaxial Cable with One Inline Type F Plug and One Type F Bulkhead Jack

CCF6-MF-1	RG6 Cable, Type F Male / Female Bulkhead, 1.0 ft
CCF6-MF-6	RG6 Cable, Type F Male / Female Bulkhead, 6.0 ft
CCF6-MF-12	RG6 Cable, Type F Male / Female Bulkhead, 12.0 ft
CCF6-MF-25	RG6 Cable, Type F Male / Female Bulkhead, 25.0 ft
CCF6-MF-50	RG6 Cable, Type F Male / Female Bulkhead, 50.0 ft