


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		L	REV PER ECR 09-027862	23DEC09	JR	TM

D

C

B

A



AMP
WIRE RANGE

16-14 AWG
SOLID OR STRANDED

- 1 STAMP AMP 16-14 APPROX AS SHOWN
- 2 WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL
- 3 NO COLOR CODING
- 4 NICKEL PER ASTM B162, ANNEALED

100	LOOSE PIECE, BOX	2 8-322329-1
5000	ON TAPE	2 2-322329-2
1000	LOOSE PIECE	3 2-322329-1
1000	LOOSE PIECE	2 322329
QTY	PACKAGE TYPE	PART NO.

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

FOR APPLICATION TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING TEMPERATURE:
649°C

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
1.04-2.62mm² [2,050-5,180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM[INCHES]

MATERIAL
- 4

FINISH
-

DWN
TA BRINKMAN
4-15-93

CHK
DA PATTERSON
4-15-93

APVD
JL MECKLEY
4-15-93

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

SCALE
10:1

SHEET
1 of 1

REV
L

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE,
HIGH TEMPERATURE,
STRATO-THERM™

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=322329

RESTRICTED TO
-