

IEC Appliance Inlet C14 with Filter, Fuseholder 1- or 2-pole, optional Voltage Selector (step switch)

Plug removal necessary for fuse replacement



Screw-on mounting from front side  
Version with ground line choke  
without voltage selector  
Fuse drawer must be ordered separately (see accessories).



Snap-in mounting from front side  
without voltage selector  
Fuse drawer must be ordered separately (see accessories).



Screw-on mounting from rear side  
without voltage selector  
Fuse drawer must be ordered separately (see accessories).



## Description

- Panel Mount:  
Screw-on version from front or rear side, snap-in version from front side
- 4 Functions:  
Appliance Inlet Protection class I, Fuseholder for fuse-links 5 x 20 mm 1- or 2-pole, with or without voltage selector (step switch), Line filter in standard and medical version
- V-Lock notch standard
- Quick connect terminals or wires

## Unique Selling Proposition

- Reduces noise on the ground wire
- Interrupts ground loops
- High asymmetrical attenuation
- V-Lock cord retaining

## Approvals

- VDE Certificate Number: 40004665 (FKE, FKF, FKV, FKW)
- UL File Number: E72928 (FKE, FKF, FKV, FKW)

## Characteristics

- Rear side mounting for efficient costsaving assembly
- Suitable for assembly in metal plated plastic housings
- All single elements are already wired
- Plug removal necessary for fuse-link replacement
- Suitable for use in equipment according to IEC/UL 60950
- Suitable for use in medical equipment according to IEC/UL 60601-1

## Other versions on request

- Capacity CX 100 nF

## References

Alternative: version without line filter [KEA](#)

Alternative: Standard version

## Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Wire Harnessing](#), [Detailed request for product](#)


## Technical Data

|                           |                                                                                |
|---------------------------|--------------------------------------------------------------------------------|
| Ratings IEC               | 1 - 10A @ Ta 40 °C / 250 VAC; 50 Hz                                            |
| Ratings UL/CSA            | 1 - 10A @ Ta 40 °C / 125 VAC; 60 Hz                                            |
| Leakage Current           | standard < 0.5 mA (250 V / 60 Hz)<br>medical < 5 µA (250 V / 60 Hz)            |
| Dielectric Strength       | > 1.7 kVDC between L-N<br>> 2.7 kVDC between L/N-PE<br>Test voltage (2 sec)    |
| Allowable Operation Temp. | -25 °C to 85 °C                                                                |
| Climatic Category         | 25/085/21 acc. to IEC 60068-1                                                  |
| Degree of Protection      | from front side IP 40 acc. to IEC 60529                                        |
| Protection Class          | Suitable for appliances with protection class I acc. to IEC 61140              |
| Terminal                  | Quick connect terminals 6.3 x 0.8 mm<br>Flexible wire AWG18, 150 mm            |
| Panel Thickness s         | Screw: max 8 mm<br>Mounting screw torque max 0.5 Nm<br>Snap-in: 0.8 mm to 3 mm |
| Material: Housing         | Thermoplastic, black, UL 94V-0                                                 |

|                                   |                                                                                                                      |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------|
| Appliance-Inlet/-Outlet           | C14 acc. to IEC 60320, UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I |
| Fuseholder                        | 1 or 2 pole, Shocksafe category PC2 acc. to IEC 60127-6, for fuse-links 5 x 20 mm                                    |
| Rated Power Acceptance @ Ta 23 °C | 5 x 20: 2W (1 pole)/ 1.6W (2-pole) per pole                                                                          |
| Power Acceptance @ Ta > 23 °C     | Admissible power acceptance at higher ambient temperature see derating curves                                        |
| Voltage Selector                  | optional, step, 3 pos.                                                                                               |
| Line Filter                       | Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8 <a href="#">Technical Details</a>                  |
| MTBF                              | > 1'700'000 h acc. to MIL-HB-217 F                                                                                   |

**Dimension**


Screw-on mounting from front side




\* with voltage selector

\*\* without voltage selector


Screw-on mounting from rear side



Snap-in mounting




### Screw-on mounting from front side with ground line choke



### Technical Data of Filter-Components


| Rated Current [A] | Filter-Type                                 | Inductance L1/<br>L2 [mH] | Inductance L3<br>[mH] | Capacitance CX<br>[nF] | Capacitance CY<br>[nF] | R [MΩ] |
|-------------------|---------------------------------------------|---------------------------|-----------------------|------------------------|------------------------|--------|
| 1                 | Standard Version                            | 2 x 10                    | -                     | 68                     | 2.2                    | -      |
| 2                 | Standard Version                            | 2 x 4                     | -                     | 68                     | 2.2                    | -      |
| 4                 | Standard Version                            | 2 x 1.5                   | -                     | 68                     | 2.2                    | -      |
| 6                 | Standard Version                            | 2 x 0.8                   | -                     | 68                     | 2.2                    | -      |
| 10                | Standard Version                            | 2 x 0.3                   | -                     | 68                     | 2.2                    | -      |
| 1                 | Standard Version with Ground Line Choke     | 2 x 10                    | 0.6                   | 100                    | 2.2                    | -      |
| 2                 | Standard Version with Ground Line Choke     | 2 x 4                     | 0.6                   | 100                    | 2.2                    | -      |
| 4                 | Standard Version with Ground Line Choke     | 2 x 1.5                   | 0.6                   | 100                    | 2.2                    | -      |
| 6                 | Standard Version with Ground Line Choke     | 2 x 0.8                   | 0.6                   | 100                    | 2.2                    | -      |
| 10                | Standard Version with Ground Line Choke     | 2 x 0.3                   | 0.6                   | 100                    | 2.2                    | -      |
| 1                 | Medical Version (M5)                        | 2 x 10                    | -                     | 68                     | -                      | 1      |
| 2                 | Medical Version (M5)                        | 2 x 4                     | -                     | 68                     | -                      | 1      |
| 4                 | Medical Version (M5)                        | 2 x 1.5                   | -                     | 68                     | -                      | 1      |
| 6                 | Medical Version (M5)                        | 2 x 0.8                   | -                     | 68                     | -                      | 1      |
| 10                | Medical Version (M5)                        | 2 x 0.3                   | -                     | 68                     | -                      | 1      |
| 1                 | Medical Version (M80)                       | 2 x 10                    | -                     | 68                     | 0.47                   | 1      |
| 2                 | Medical Version (M80)                       | 2 x 4                     | -                     | 68                     | 0.47                   | 1      |
| 4                 | Medical Version (M80)                       | 2 x 1.5                   | -                     | 68                     | 0.47                   | 1      |
| 6                 | Medical Version (M80)                       | 2 x 0.8                   | -                     | 68                     | 0.47                   | 1      |
| 10                | Medical Version (M80)                       | 2 x 0.3                   | -                     | 68                     | 0.47                   | 1      |
| 1                 | Medical Version (M5) with Ground Line Choke | 2 x 10                    | 0.15                  | 100                    | -                      | 1      |
| 2                 | Medical Version (M5) with Ground Line Choke | 2 x 4                     | 0.6                   | 100                    | -                      | 1      |
| 4                 | Medical Version (M5) with Ground Line Choke | 2 x 1.5                   | 0.6                   | 100                    | -                      | 1      |
| 6                 | Medical Version (M5) with Ground Line Choke | 2 x 0.8                   | 0.6                   | 100                    | -                      | 1      |
| 10                | Medical Version (M5) with Ground Line Choke | 2 x 0.3                   | 0.15                  | 100                    | -                      | 1      |

## Diagrams


Standard version  
with voltage selector

x) external connection to be made by the customer

- 1) Line  
2) Load


Standard version  
without voltage selector

- 1) Line  
2) Load


Medical version (M5)  
with voltage selector

x) external connection to be made by the customer

- 1) Line  
2) Load


Medical version (M5)  
without voltage selector

- 1) Line  
2) Load

Medical version (M80)  
with voltage selector


x) external connection to be made by the customer

- 1) Line  
2) Load

Medical version (M80)  
without voltage selector


- 1) Line  
2) Load

Standard version with ground line choke




- 1) Line  
2) Load

Medical version (M5) with ground line choke



- 1) Line  
2) Load


Medical version (M80) with ground line choke




- 1) Line  
2) Load

## Derating Curves

1-pole



2-pole




## Attenuation Loss


Standard version

- - - differential mode \_\_\_\_\_ common mode

1 A




2 A




---


4 A



6 A




10 A




Medical version (M5)

1 A




2 A




---


4 A



6 A




10 A




Medical version (M80)


1 A




2 A




4 A



6 A




10 A




## Standard with Earth Line Choke


1 A




2 A




4 A



6 A




10 A




## Medical (M5) with Earth Line Choke


1 A




2 A




4 A



6 A



10 A



## All Variants

| Rated Current [A] | Filter-Type      | Panel mounting | Mounting side | Fuseholder | Terminal                             | Voltage Selector | Order Number |
|-------------------|------------------|----------------|---------------|------------|--------------------------------------|------------------|--------------|
| 1                 | Standard Version | Snap-in        | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6011    |
| 1                 | Standard Version | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6001    |
| 2                 | Standard Version | Snap-in        | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6012    |
| 2                 | Standard Version | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6002    |
| 4                 | Standard Version | Snap-in        | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6013    |
| 4                 | Standard Version | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6003    |
| 6                 | Standard Version | Snap-in        | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6014    |
| 6                 | Standard Version | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6004    |
| 10                | Standard Version | Snap-in        | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6015    |
| 10                | Standard Version | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6005    |
| 1                 | Standard Version | Screw          | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5011    |
| 1                 | Standard Version | Screw          | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5051    |

| Rated Current<br>[A] | Filter-Type                             | Panel mounting | Mounting<br>side | Fuseholder | Terminal                             | Voltage Selector | Order Number |
|----------------------|-----------------------------------------|----------------|------------------|------------|--------------------------------------|------------------|--------------|
| 1                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5001    |
| 1                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5041    |
| 1                    | Standard Version                        | Screw          | Rear Side        | 1-pole     | Flexible wire AWG18                  | -                | 4301.7311    |
| 1                    | Standard Version                        | Screw          | Rear Side        | 2-pole     | Flexible wire AWG18                  | -                | 4301.7301    |
| 1                    | Standard Version                        | Screw          | Rear Side        | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7001    |
| 2                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5012    |
| 2                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5052    |
| 2                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5002    |
| 2                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5042    |
| 2                    | Standard Version                        | Screw          | Rear Side        | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7002    |
| 4                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5013    |
| 4                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5053    |
| 4                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5003    |
| 4                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5043    |
| 4                    | Standard Version                        | Screw          | Rear Side        | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7013    |
| 4                    | Standard Version                        | Screw          | Rear Side        | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7003    |
| 6                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5014    |
| 6                    | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5054    |
| 6                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5004    |
| 6                    | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5044    |
| 6                    | Standard Version                        | Screw          | Rear Side        | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7014    |
| 6                    | Standard Version                        | Screw          | Rear Side        | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7004    |
| 10                   | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5015    |
| 10                   | Standard Version                        | Screw          | Front Side       | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5055    |
| 10                   | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5005    |
| 10                   | Standard Version                        | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5045    |
| 10                   | Standard Version                        | Screw          | Rear Side        | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7015    |
| 10                   | Standard Version                        | Screw          | Rear Side        | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7005    |
| 1                    | Standard Version with Ground Line Choke | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8050    |
| 2                    | Standard Version with Ground Line Choke | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8051    |
| 4                    | Standard Version with Ground Line Choke | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8052    |
| 6                    | Standard Version with Ground Line Choke | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8053    |
| 10                   | Standard Version with Ground Line Choke | Screw          | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8054    |
| 1                    | Medical Version (M5)                    | Snap-in        | Front Side       | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6201    |

| Rated Current [A] | Filter-Type                                 | Panel mounting | Mounting side | Fuseholder | Terminal                             | Voltage Selector | Order Number |
|-------------------|---------------------------------------------|----------------|---------------|------------|--------------------------------------|------------------|--------------|
| 2                 | Medical Version (M5)                        | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6203    |
| 4                 | Medical Version (M5)                        | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6205    |
| 6                 | Medical Version (M5)                        | Snap-in        | Front Side    | 2-pole     | Flexible wire AWG18                  | -                | 4301.6307    |
| 6                 | Medical Version (M5)                        | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6207    |
| 1                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5241    |
| 1                 | Medical Version (M5)                        | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7201    |
| 2                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5203    |
| 2                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5243    |
| 2                 | Medical Version (M5)                        | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7203    |
| 4                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5205    |
| 4                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5245    |
| 4                 | Medical Version (M5)                        | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7205    |
| 6                 | Medical Version (M5)                        | Screw          | Front Side    | 1-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5217    |
| 6                 | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5247    |
| 6                 | Medical Version (M5)                        | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7207    |
| 10                | Medical Version (M5)                        | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5209    |
| 10                | Medical Version (M5)                        | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7209    |
| 4                 | Medical Version (M80)                       | Snap-in        | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.6206    |
| 1                 | Medical Version (M80)                       | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7202    |
| 2                 | Medical Version (M80)                       | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5204    |
| 2                 | Medical Version (M80)                       | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | 3 pos.           | 4301.5244    |
| 2                 | Medical Version (M80)                       | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7204    |
| 4                 | Medical Version (M80)                       | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5206    |
| 4                 | Medical Version (M80)                       | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7206    |
| 6                 | Medical Version (M80)                       | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7208    |
| 10                | Medical Version (M80)                       | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.5200    |
| 10                | Medical Version (M80)                       | Screw          | Rear Side     | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.7200    |
| 1                 | Medical Version (M5) with Ground Line Choke | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8055    |
| 2                 | Medical Version (M5) with Ground Line Choke | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8056    |
| 4                 | Medical Version (M5) with Ground Line Choke | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8057    |
| 6                 | Medical Version (M5) with Ground Line Choke | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8058    |
| 10                | Medical Version (M5) with Ground Line Choke | Screw          | Front Side    | 2-pole     | Quick connect terminals 6.3 x 0.8 mm | -                | 4301.8059    |

Most Popular:

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Wire length: 150 mm

Packaging unit 10 Pcs

## Required Accessory

### Description

#### Fusedrawer 2

Fusedrawer für Fuse Links 5x20 mm, with or without Voltage Selector Insert



|                                                     |              |
|-----------------------------------------------------|--------------|
| Fingergrip, 2-pole, Voltage Selector, 110, 150, 220 | 4301.1014.01 |
| Fingergrip, 2-pole, Voltage Selector, 120, 240      | 4301.1014.02 |
| Fingergrip, 2-pole, Voltage Selector, 110, 220      | 4301.1014.03 |
| Fingergrip, 2-pole, Voltage Selector, 115, 220      | 4301.1014.04 |


...

## Accessories



#### Wire Harness

Wire harness for SCHURTER products



#### Assorted Covers

Rear Cover

0859.0072



#### Cord retaining kits

Cord retaining strain relief

|                |           |
|----------------|-----------|
| Flat head, A   | 4700.0001 |
| Countersunk, B | 4700.0002 |

## Mating Outlets/Connectors

### Category / Description

#### Appliance Outlet Overview complete



|                                                                                                   |      |
|---------------------------------------------------------------------------------------------------|------|
| IEC Appliance Outlet F, Screw-on Mounting, Front Side, Solder Terminal                            | 4787 |
| IEC Appliance Outlet F, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal            | 4788 |
| IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal | 5091 |

[Appliance Outlet further types to KFA](#)



Connector Overview complete

|                                                                                 |         |
|---------------------------------------------------------------------------------|---------|
| 4782 Mounting: Power Cord, 3 x 1 mm² / 3 x 18 AWG, Cable, Connector: IEC C13    | 4782    |
| 4022 Mounting: Power Supply Cord, 3 x 1.5 mm², Screw clamps, Connector: IEC C13 | 4022    |
| 4785 Mounting: Power Cord, 3 x 1 mm² / 3 x 18 AWG, Cable, Connector: IEC C13    | 4785    |
| 4300-06 Mounting: Power Cord, 3 x 1 mm² / 3 x 18 AWG, Cable, Connector: IEC C13 | 4300-06 |
| 4012 Mounting: Power Supply Cord, 3 x 1.5 mm², Screw clamps, Connector: IEC C13 | 4012    |
| Connector further types to KFA                                                  | ...     |

Mating Outlets/Connectors shuttered



Power Cord Overview complete

|                                                         |           |
|---------------------------------------------------------|-----------|
| VAC17KS, North America, 2.0 m, Connector C17, cord end: | 6051.2801 |
| VAC17KS, Europlug, 2.0 m, Connector IEC C17, cord end:  | 6051.2803 |
| VAC17KS, Europlug, 2.0 m, Connector IEC C17, cord end:  | 6051.2813 |
| VAC13KS, Overview, diverse Connector IEC C13, cord end: | VAC13KS   |
| Power Cord further types to KFA                         |           |