



Sample photo

Order symbol: ABS B 65 G
Product nbr: 8784303
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074001993
El. number:
 Finland 3423451
 Denmark 8212001802
 Italy 7211010
 Sweden 2536701

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		L	W	H	Rating:
mm:		110	80	65	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 6P, 12, 13
inch:		4.3	3.1	2.6	
Materials:					
Material:		ABS			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
B-MP		Mounting plate			
B-3		DIN-35 Mounting rail			
FP 22040		Mounting foot kit (2 pcs)			

