

PRODUCTS

Large Cabinet Racks

Communications
Cabinets/Racks

Cabinets

Open Racks

Chassis

Small Metal Enclosures

Die Cast Boxes

Plastic Boxes

NEMA Boxes
(Water-tight Plastic and
Fiberglass)

NEMA Boxes
(Water-tight Sheet Metal)

NEMA Boxes
(Water-tight Aluminum)

Accessories

Brackets

Custom Products

Cabinets
Classic II



Click on Image for Larger View

Whether used independently or as a companion to the Classic II cabinet rack, the design of this distinctive cabinet harmonizes perfectly with the most sophisticated systems. While it is portable, it is equally effective for permanent installations.

Design Features

- *Top, bottom and side panels .05" aluminum. Frame, 6063 - T5 aluminum extrusions.
- *Accommodate 19.00" panels.
- *Panel Mounting Rails have #10 - 32 tapped holes on E.I.A. spacing (Use #7346 screws - order separately)
- *Panels not included but are available.
- *.09" aluminum alloy doors attach to mounting rails and have black thermoplastic flush type latches.
- *Cabinet - 500# equipment load capacity. Carrying Handles limited to 100# capacity.

Bonus Features

- *Recessed handles are attached to two steel flanges extending the length of the cabinet. This added support assures carrying safety.
- * Two 16 - gauge steel vertically adjustable chassis supports included.
- *Shipped completely assembled.

Finishes

Gray Texture (GT) Royal Blue Texture (RB) . Available in other Bud Textured Finishes at no extra cost.

Classic II- Cabinets & Doors						
Catalog Numb	Drawings	Heigh	Panel Space	Weigh (Lbs.)	Door Catalog Numb	Weigh (Lbs.)
AGC-9268	PDF DXF	8.81"	7.00"	30	AGD-368	2.00
AGC-9269	PDF DXF	10.56'	8.75"	32	AGD-369	2.75
AGC-9270	PDF DXF	12.31'	10.50'	33	AGD-370	3.00
AGC-9271	PDF DXF	14.06'	12.25'	34	AGD-371	3.50
AGC-9272	PDF DXF	15.81'	14.00'	35	AGD-372	4.00
AGC-9273	PDF DXF	17.56'	15.75'	36	AGD-373	4.75
AGC-9274	PDF DXF	19.31'	17.50'	37	AGD-374	5.00
AGC-9275	PDF DXF	21.06'	19.25'	39	AGD-375	5.50
AGC-9276	PDF DXF	22.81'	21.00'	40	AGD-376	6.25
AGC-9277	PDF DXF	24.56'	22.75'	41	AGD-377	6.75
AGC-9278	PDF DXF	26.31'	24.50'	42	AGD-378	7.25
AGC-9279	PDF DXF	28.06'	26.25'	43	AGD-379	7.50
AGC-9280	PDF DXF	29.81'	28.00'	45	AGD-380	8.00

[DXF](#) Autocad DXF Specifications File (Requires CAD software such as AutoCAD) [PDF](#) Adobe PDF Specifications File



Download PDF Viewer