



SSMT Surface Mount Interconnect System (Continued)**Inter-Series Cable Assemblies****Notes:**

1. Consult AMP for non-standard cable lengths:
Length A Tolerances.

Length A	Tolerance
50 To 100 (3.94)	± 3 ($\pm .12$)
101 To 500 (3.98 to 19.69)	$+ 5$ ($+ .20$)
Over 500 (19.69)	± 10 ($\pm .39$)


2. Connectors are randomly aligned unless otherwise noted.
3. SSMT Jack is not mateable with OSMT High Retention Plug receptacle (1055690-1).

SMA Straight Plug


Assembly Length (A)	M/A-COM Model No.	Part No.
100 [4.0]	9960-4100-01	1064543-1
200 [8.0]	9960-4200-01	1064552-1
305 [12.0]	9960-4305-01	1064560-1

Note:

1064552-1 recommended for customer system verification.

SMA Bulkhead Jack

Assembly Length (A)	M/A-COM Model No.	Part No.
100 [4.0]	9960-4100-02	1064544-1
200 [8.0]	9960-4200-02	1064553-1
305 [12.0]	9960-4305-02	1064561-1

SMB Straight Plug

Assembly Length (A)	M/A-COM Model No.	Part No.
100 [4.0]	9960-4100-03	1064545-1
200 [8.0]	9960-4200-03	1064554-1
305 [12.0]	9960-4305-03	1064562-1