

Honeywell Sensing and Control

Search


[narrow your search](#)

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9736)

Technology

- Control and Instrumentation (1063)
- Electromechanical (9297)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

192-222LET-A01 Discrete Thermistors

(Home : Products)



Actual product appearance may vary.

192 Series, Uni-Curve with bare leads and epoxy, 2,252 Ohm resistance, $\pm 0,2$ °C [0.36 °F] tolerance, 25/85 BETA = 3974

[Sales & Service](#)
[Distributor Inventory](#)

Need Help?

[Click here to contact us](#)
[Overview](#)[Specs](#)[Documentation](#)[Application Notes](#)

Product Specifications

Availability	Global
Resistance	2,252 Ohm
Tolerance	$\pm 0,2$ °C [0.36 °F]
Accuracy	0 °C to 70 °C [32 °F to 158 °F]
Beta	3974
Operating Temperature	-60 °C to 150 °C [-76 °F to 302 °F]
Diameter	2,413 mm [0.095 in]
Termination Material	32 Gauge tinned copper, alloy 180
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	15.0 s
Dissipation Constant	0,75 m/W°C
Series Name	192