

## PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

### ELFA artikelnr

|                  |                                    |                  |                                  |
|------------------|------------------------------------|------------------|----------------------------------|
| <b>48-719-92</b> | <b>Glidskena 0201 406mm</b>        | <b>48-726-02</b> | <b>Mont.vinklar botten 350mm</b> |
| <b>48-720-40</b> | <b>Glidskena 0201 610mm</b>        | <b>48-726-10</b> | <b>Mont.vinklar botten 400mm</b> |
| <b>48-721-07</b> | <b>Glidskena 0204 406mm</b>        | <b>48-726-28</b> | <b>Mont.vinklar botten 450mm</b> |
| <b>48-721-49</b> | <b>Glidskena 0204 610mm</b>        | <b>48-726-36</b> | <b>Mont.vinklar botten 500mm</b> |
| <b>48-722-06</b> | <b>Glidskena 0301 406mm</b>        | <b>48-726-44</b> | <b>Mont.vinklar botten 550mm</b> |
| <b>48-722-48</b> | <b>Glidskena 0301 610mm</b>        | <b>48-727-01</b> | <b>Universalvinkel 63310</b>     |
| <b>48-723-05</b> | <b>Glidskena 3307 305mm</b>        | <b>48-727-19</b> | <b>Vinklar fram 63060</b>        |
| <b>48-723-13</b> | <b>Glidskena 3307 356mm</b>        | <b>48-727-27</b> | <b>Vinklar bak 28mm 63070</b>    |
| <b>48-723-21</b> | <b>Glidskena 3307 406mm</b>        | <b>48-727-35</b> | <b>Vinklar bak 220mm 63250</b>   |
| <b>48-723-39</b> | <b>Glidskena 3307 457mm</b>        | <b>48-727-43</b> | <b>Mutterlist 66010</b>          |
| <b>48-723-47</b> | <b>Glidskena 3307 508mm</b>        | <b>48-728-00</b> | <b>Kabelhållare CC5AD</b>        |
| <b>48-723-54</b> | <b>Glidskena 3307 559mm</b>        |                  |                                  |
| <b>48-723-62</b> | <b>Glidskena 3307 610mm</b>        |                  |                                  |
| <b>48-723-70</b> | <b>Glidskena 3307 660mm</b>        |                  |                                  |
| <b>48-723-88</b> | <b>Glidskena 3307 711mm</b>        |                  |                                  |
| <b>48-725-03</b> | <b>Glidskena 3832 250mm (3831)</b> |                  |                                  |
| <b>48-725-11</b> | <b>Glidskena 3832 300mm (3831)</b> |                  |                                  |
| <b>48-725-29</b> | <b>Glidskena 3832 400mm (3831)</b> |                  |                                  |
| <b>48-725-37</b> | <b>Glidskena 3832 450mm (3831)</b> |                  |                                  |
| <b>48-725-45</b> | <b>Glidskena 3832 500mm (3831)</b> |                  |                                  |
| <b>48-725-52</b> | <b>Glidskena 3832 550mm (3831)</b> |                  |                                  |
| <b>48-725-60</b> | <b>Glidskena 3832 600mm (3831)</b> |                  |                                  |
| <b>48-725-78</b> | <b>Glidskena 3832 650mm (3831)</b> |                  |                                  |
| <b>48-725-86</b> | <b>Glidskena 3832 700mm (3831)</b> |                  |                                  |
| <b>48-725-94</b> | <b>Glidskena 3832 350mm (3831)</b> |                  |                                  |

# Your Guide to Slide Selection

## Factors to consider in selecting a slide

- Weight of chassis/drawer
- Side space available between chassis/drawer and rack/cabinet
- Depth of chassis/drawer
- Depth of rack/cabinet
- Height of chassis/drawer
- Travel/extension desired
- Is quick disconnect required?
- Lock function required
- Mounting hole pattern required
- Optional mounting hardware for mounting into rack/enclosure
- Any specialised applicational or environmental requirements

**Accuride**  
reserve the right to  
alter specifications  
without notice.

# Slide Selection

## IF YOUR MAJOR CONSIDERATION IS LOAD OR SPACE

| Maximum Load Rating Per Pair<br>(Based on Slide Length - refer to product data page) | Side Space Required           | Slide Type | Page No. |
|--------------------------------------------------------------------------------------|-------------------------------|------------|----------|
| 34 kg                                                                                | 12.7 mm                       | 0262       | 24       |
| 45 kg                                                                                | 12.7 mm                       | 3831       | 11       |
| 49 kg                                                                                | 9.5 mm                        | 0201       | 9        |
| 59 kg                                                                                | 9.5 mm                        | 0204       | 10       |
| 59 kg                                                                                | 19.1 mm (10.00mm if recessed) | 0305       | 12       |
| 63 kg                                                                                | 19.1 mm                       | 0307       | 13       |
| 65 kg                                                                                | 19.1 mm                       | 0330       | 25       |
| 68 kg                                                                                | 12.7 mm                       | 3307       | 14       |
| 68 kg                                                                                | 12.7 mm                       | 3308       | 15       |
| 80 kg                                                                                | 19.1 mm                       | 0301       | 16       |
| 113.5 kg                                                                             | 12.7 mm                       | 0601       | 22       |
| 124 kg                                                                               | 19.1 mm                       | 3607       | 17       |
| 180 kg                                                                               | 19.1 mm                       | 0531       | 18       |
| 227 kg                                                                               | 19.1 mm                       | 9301       | 20       |
| 230 kg                                                                               | 26.5 mm                       | 0522       | 23       |
| 272 kg                                                                               | 23.6 mm                       | 0501       | 19       |
| 420 kg                                                                               | 23.6 mm                       | 0530       | 21       |

Models highlighted are also available via the  
**Accuride**  
**QUICKSHIP**  
PROGRAMME

See individual product page for specific load rating per length.

## Basis of Load Ratings

- The maximum permissible load for a pair of side mounted slides
- The centre of gravity of load is centred between and at the midpoint of the drawer members
- Based on 10,000 cycle dynamic tests
- Includes additional 100% static load safety factor in the extended position
- Flat mounting the slides reduces load carrying capacity to approximately 25% of the side mount capacity.
- All fixing positions should be used to achieve maximum load rating.
- For any specialised application which is exposed to vibration and/or rough usage e.g. mobile vehicles or military equipment or where the frequency of access is high, the load ratings quoted may not be applicable. We therefore recommend that in all such applications you consult with Accuride or your local Accuride representative to determine product suitability.

Slide Selection

# Standard Slide Specification & Ordering Guidelines

## Material Specification

|                                        |                                                          |
|----------------------------------------|----------------------------------------------------------|
| Slide members                          | - cold rolled steel                                      |
| Ball retainers                         | - cold rolled steel zinc plated or stainless steel       |
| Ball bearings                          | - precision type, carbon chrome steel or stainless steel |
| Lubricant                              | - Hi-Lo temperature grease                               |
| Stainless Steel - 1.4301 X 5 CrNi 1810 |                                                          |

## General Technical Information

- Tolerances unless otherwise stated are  $\pm 0.8$  on linear or  $\pm 0.2$  on diameter.
- Internal clearances permit screw head dimensions not exceeding 2.5mm high x 9.6mm diameter (on the 9301 outer member and the 0531 - only the M5 countersunk screw may be used).
- Holes other than shown may be in the members at Accuride option.

## How to Order

Accuride slides are available in the following standard finishes and packaging:-

| Order Prefix | Packaging                                        | Finish                                                                           |
|--------------|--------------------------------------------------|----------------------------------------------------------------------------------|
| <b>DZ</b>    | Quick Ship (ex. stock)<br>(packed in pairs/kits) | Electro zinc plate and clear chromate                                            |
| <b>CZ</b>    | Manufactured to order<br>(bulk-packed)           | Electro zinc plate and clear chromate                                            |
| <b>DB</b>    | Quick Ship (ex. stock)<br>(packed in pairs/kits) | Electro zinc plate and black passivate                                           |
| <b>CB</b>    | Manufactured to order<br>(bulk-packed)           | Electro zinc plate and black passivate                                           |
| <b>DS</b>    | Quick Ship (ex. stock)<br>(packed in pairs/kits) | Stainless Steel<br>see table below for models available                          |
| <b>SS</b>    | Manufactured to Order<br>(bulk-packed)           | Stainless Steel<br>see table below for models available                          |
| <b>CY</b>    | Manufactured to Order<br>(bulk-packed)           | Electro-zinc plate and yellow chromate                                           |
| <b>MY</b>    | Manufactured to Order<br>(bulk-packed)           | Electro-zinc plate and yellow chromate with stainless steel balls and retainers. |

N.B. Other packaging and finish options may be available - please contact Accuride for details.

## Your Accuride ordering code is made up as follows:-

|                                                                            |             |              |                                              |
|----------------------------------------------------------------------------|-------------|--------------|----------------------------------------------|
| <b>DZ</b>                                                                  | <b>0301</b> | <b>-0018</b> | <b>LJ</b>                                    |
| Denotes whether stock or manufactured and desired finish (see above table) | Slide Model | Slide Length | Accessory (flip-loc and shockblock options). |

## For Example:

### SS0501-0020LJ

Would be slide model 0501 manufactured to order in stainless steel @ 20" (508 mm) long. With a lock open and closed flip-loc (2354 series - see page 30).

### DZ0301-0016

Would be slide model 0301 in bright zinc finish supplied from the Quick Ship Programme (ex. Stock) @ 16" (406 mm) long.

- IF FLIP-LOKS AND/OR SHOCKBLOCKS ARE REQUIRED A SUFFIX WILL NEED TO BE ADDED TO THE ORDER CODE. FOR DETAILS SEE PAGES 29 & 30

# Slide Specification

| STANDARD FEATURES        | GENERAL PURPOSE RANGE |                       |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |
|--------------------------|-----------------------|-----------------------|------------------------|-----------------------|-----------------------|------------------------|------------------------|-----------------------|------------------------|-----------------------|------------------------|-----------------------|-----------------------|
|                          | 201<br><i>Page 9</i>  | 204<br><i>Page 10</i> | 3831<br><i>Page 11</i> | 305<br><i>Page 12</i> | 307<br><i>Page 13</i> | 3307<br><i>Page 14</i> | 3308<br><i>Page 15</i> | 301<br><i>Page 16</i> | 3607<br><i>Page 17</i> | 531<br><i>Page 18</i> | 9301<br><i>Page 20</i> | 501<br><i>Page 19</i> | 530<br><i>Page 21</i> |
| 75% Extension            | <div></div>           | <div></div>           |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |
| 100% Extension           |                       |                       |                        |                       |                       |                        |                        |                       | <div></div>            |                       | <div></div>            |                       |                       |
| 100%+ Extension          |                       |                       | <div></div>            | <div></div>           | <div></div>           | <div></div>            | <div></div>            | <div></div>           |                        | <div></div>           |                        | <div></div>           | <div></div>           |
| Two-Way Travel           |                       |                       |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |
| Front Disconnect         |                       | <div></div>           | <div></div>            | <div></div>           | <div></div>           | <div></div>            | <div></div>            |                       | <div></div>            |                       |                        |                       |                       |
| Hold-in Detent           |                       |                       | <div></div>            |                       |                       |                        |                        |                       |                        | <div></div>           |                        |                       |                       |
| Lock-in                  |                       |                       |                        |                       |                       |                        | <div></div>            |                       |                        |                       |                        |                       |                       |
| Lock-out                 |                       | <div></div>           |                        | <div></div>           | <div></div>           | <div></div>            | <div></div>            |                       | <div></div>            |                       |                        |                       |                       |
| Shock Blocks as Standard |                       |                       |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |
| Stainless Steel          |                       |                       |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |
| Linear Movement          |                       |                       |                        |                       |                       |                        |                        |                       |                        |                       |                        |                       |                       |

## OPTIONAL FEATURES

|                                   |   |   |   |   |   |   |   |   |   |    |  |   |   |
|-----------------------------------|---|---|---|---|---|---|---|---|---|----|--|---|---|
| Optional Bottom/Platform Mount    |   |   | ● |   |   |   |   |   |   |    |  |   |   |
| Optional Rack Mounting Brackets   | ● | ● |   | ● | ● | ● | ● | ● | ● | ●  |  | ● |   |
| Also available in Stainless Steel | ● | ● |   |   |   |   |   | ● |   | ●* |  | ● | ● |
| Shock Blocks available            | ● |   |   |   |   |   |   | ● |   |    |  | ● | ● |
| Flip-locks available              |   |   |   |   |   |   |   | ● |   |    |  | ● | ● |

| SPECIALIST RANGE |                |                |                |                |
|------------------|----------------|----------------|----------------|----------------|
| 115<br>Page 28   | 601<br>Page 22 | 522<br>Page 23 | 262<br>Page 24 | 330<br>Page 25 |
|                  |                |                |                |                |
|                  |                |                |                |                |
|                  |                | ●              | ●              | ●              |
|                  | ●              |                |                |                |
|                  |                |                |                |                |
|                  |                |                | ●              | ●              |
|                  |                |                |                |                |
|                  |                | ●              |                |                |
|                  |                |                |                | ●              |
| ●                |                |                |                |                |

Models also available in the  
**Accuride**  
**QUICKSHIP**  
PROGRAMME

Optional features also available in the  
**Accuride**  
**QUICKSHIP**  
PROGRAMME

**Accuride**  
reserve the right to  
alter specifications  
without notice.

Refer to individual product page for more information. See page 8 for explanation of terms.

\* Available up to 500mm length only.

Slide Specification

# Explanation of Terms

**Side Space** The amount of room necessary between the drawer side and the cabinet or chassis and the rack. The side space dimension is critical for optimal smooth movement. Special brackets are available to reduce the side space required in an electronics rack with model 305. These brackets allow a portion of the slide to be mounted behind the vertical rail. See page 12 for details.

**Travel**

|                        |                                                                                                                             |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| <b>75% extension</b>   | Drawer opens partially, approximately 75% of the total slide length.                                                        |
| <b>100% extension</b>  | Drawer opens the same amount again as the slide length.                                                                     |
| <b>100%+ extension</b> | Overtravel is achieved. This allows the drawer to pull completely out of the cabinet providing access to the entire drawer. |

**Disconnect** Allows the drawer or chassis to be quickly removed from the case or rack. A lever or latch must be actuated before the drawer can be removed from the cabinet.

**Detent** Holds the slide open or closed until extra force is applied to overcome the detent.

**Locks** Secures the slide in position. A lever or latch must be actuated to move the slide. A lock-out feature assists servicing components without removing the unit from the enclosure. A lock-in feature prevents drawers from opening until a latch is actuated.

**Optional Rack Mounting Brackets** Optional brackets are available to make it easier to mount slides in an electronics rack/enclosure. Please refer to rack mounting accessories selection guide on page 31-34.

**Shock Blocks** Accuride shock blocks are hardened steel pins which provide an interference fit between the slide members to effectively minimise the amplification of vibration and reduce the damaging effects of shock.



**Flip-loks** 300 and 500 series slides may be supplied with the "Flip-loks". Locked positions can be provided at the open, closed and 1/2 travel locations, separately or in any combination. Manually operated, the lock series provides both local and remote actuation. Design simplicity and rugged construction ensures a high degree of reliability.

*Accuride®*

*Accuride®  
reserve the right to  
alter specifications  
without notice.*

# Accuride®

## 75% extension slide



See page 6 - 'How to Order' - to select your desired finish and packaging.

### FEATURES

- 75% extension
- Slide assembly is unhandred
- See pages 31-34 for rack mounting bracket options
- See page 7 for optional features
- Quick Ship finish available is Bright Zinc. For other finishes available see page 6

| ORDER CODE  | DIMENSIONS   |             |       |       |       |       |       |       |       | KILOGRAMS PER PAIR |             |
|-------------|--------------|-------------|-------|-------|-------|-------|-------|-------|-------|--------------------|-------------|
|             | SLIDE LENGTH | TRAVEL ±3.2 | A     | B     | C     | D     | E     | F     | G     | SLIDE WEIGHT       | LOAD RATING |
| --0201-0012 | 304.8        | 226.5       | -     | 152.4 | 254.0 | -     | 149.2 | 260.3 | 273.0 | 0.57               | 49          |
| --0201-0014 | 355.6        | 277         | -     | 203.2 | 304.8 | -     | 200.0 | 311.2 | 323.9 | 0.66               | 47          |
| --0201-0016 | 406.4        | 302.5       | -     | 254.0 | 355.6 | -     | 250.8 | 361.9 | 374.6 | 0.77               | 43          |
| --0201-0018 | 457.2        | 328         | 203.2 | 304.8 | 406.4 | 212.7 | 301.6 | 412.7 | 425.4 | 0.87               | 41          |
| --0201-0020 | 508.0        | 379         | 228.6 | 355.6 | 457.2 | 238.1 | 352.4 | 463.5 | 476.2 | 0.96               | 37          |
| --0201-0022 | 558.8        | 404         | 254.0 | 406.4 | 508.0 | 263.5 | 403.2 | 514.3 | 527.0 | 1.06               | 34          |
| --0201-0024 | 609.6        | 429.5       | 279.4 | 457.2 | 558.8 | 288.9 | 454.0 | 565.1 | 577.8 | 1.17               | 30          |
| --0201-0026 | 660.4        | 480.5       | 304.8 | 508.0 | 609.6 | 314.3 | 504.8 | 615.9 | 628.6 | 1.25               | 27          |
| --0201-0028 | 711.2        | 505.5       | 330.2 | 558.8 | 660.4 | 339.7 | 555.6 | 666.7 | 679.4 | 1.34               | 25          |

Order codes with this tint indicate Quick Ship lengths currently held in stock

### NOTES

- Dimensions in millimetres.
- All fixing positions must be used to achieve maximum load rating
- It may be possible to manufacture alternative lengths to order. Contact your local Accuride representative for details.



Technical drawing of a rectangular metal part. The drawing shows a side view of the part, which has a rectangular shape with rounded ends. The dimensions are indicated: a vertical dimension of 35.3 and a horizontal dimension of 9.5. The part is shown in a perspective view, with a dashed line indicating the hidden edge.

[illegible]

## FEATURES

- 75% extension
- Slide has lock out
- Chassis member disconnects
- Slide assembly is unhandred
- See pages 31-34 for rack mounting bracket options
- See page 7 for optional features
- Quick Ship finish available is Bright Zinc. For other finishes available see page 6

| ORDER<br>CODE | DIMENSIONS      |                |       |       |       |       |       |       |       | KILOGRAMS<br>PER PAIR |                |
|---------------|-----------------|----------------|-------|-------|-------|-------|-------|-------|-------|-----------------------|----------------|
|               | SLIDE<br>LENGTH | TRAVEL<br>±3.2 | A     | B     | C     | D     | E     | F     | G     | SLIDE<br>WEIGHT       | LOAD<br>RATING |
| --0204-0012   | 304.8           | 201.5          | -     | 215.9 | 254.0 | -     | 136.5 | 247.7 | 260.4 | 0.63                  | 64             |
| --0204-0014   | 355.6           | 252.5          | -     | 266.7 | 304.8 | -     | 187.3 | 298.5 | 311.2 | 0.73                  | 59             |
| --0204-0016   | 406.4           | 303.0          | -     | 317.5 | 355.6 | -     | 238.1 | 349.2 | 361.9 | 0.84                  | 55             |
| --0204-0018   | 457.2           | 329.0          | 203.2 | 342.9 | 406.4 | 200.0 | 288.9 | 400.0 | 412.7 | 0.94                  | 50             |
| --0204-0020   | 508.0           | 379.5          | 228.6 | 393.7 | 457.2 | 225.4 | 339.7 | 450.8 | 463.5 | 1.05                  | 42             |
| --0204-0022   | 558.8           | 405.0          | 254.0 | 419.1 | 508.0 | 250.8 | 390.5 | 501.6 | 514.3 | 1.15                  | 39             |
| --0204-0024   | 609.6           | 430.5          | 279.4 | 444.5 | 558.8 | 276.2 | 441.3 | 552.4 | 565.1 | 1.27                  | 35             |
| --0204-0026   | 660.4           | 481.5          | 304.8 | 495.3 | 609.6 | 301.6 | 492.1 | 603.3 | 616.0 | 1.37                  | 32             |
| --0204-0028   | 711.2           | 506.5          | 330.2 | 520.7 | 660.4 | 327.0 | 542.9 | 654.1 | 666.8 | 1.47                  | 27             |



Order codes with this tint indicate Quick Ship lengths currently held in stock

## NOTES

- Dimensions in millimetres.
- All fixing positions must be used to achieve maximum load rating.
- It may be possible to manufacture alternative lengths to order. Contact your local Accuride representative for details.

# Accuride®

## 100%+ extension slide with optional clip-on platform and bottom mount bracket




### FEATURES

- 100%+ extension
- Optional clip-on bottom mount bracket for lengths 350mm - 550mm
- Platform mounting option
- Drawer member disconnects by rotating lever
- Stay closed feature
- Tolerance absorption tabs
- Quick Ship finishes available are Bright Zinc and Black Passivate. For other finishes available see page 6

### NOTES

- Dimensions in millimetres.
- All fixing positions must be be used to achieve maximum load rating
- It may be possible to manufacture alternative lengths to order. Contact your local Accuride representative for details.

Accuride®  
reserve the right to  
alter specifications  
without notice.




See page 6 - 'How to Order' - to select your desired finish and packaging.

| ORDER CODE  | DIMENSIONS |     |      |     |     |     |     |     |    |     |     |     | KILOGRAMS PER PAIR |             |
|-------------|------------|-----|------|-----|-----|-----|-----|-----|----|-----|-----|-----|--------------------|-------------|
|             | SL         | TR  | A    | B   | C   | D   | E   | F   | G  | H   | I   | J   | SLIDE WEIGHT       | LOAD RATING |
| --3831-0025 | 250        | 243 | 96.0 | -   | -   | -   | -   | 192 | -  | -   | -   | -   | 0.79               | 23          |
| --3831-0030 | 300        | 305 | 96.0 | -   | -   | -   | -   | 242 | 11 | 224 | -   | -   | 0.95               | 27          |
| --3831-0035 | 350        | 356 | 128  | -   | -   | -   | -   | 292 | 11 | 224 | -   | -   | 1.10               | 34          |
| --3831-0040 | 400        | 406 | 128  | -   | -   | -   | -   | 342 | 11 | 224 | 320 | -   | 1.27               | 45          |
| --3831-0045 | 450        | 457 | 128  | -   | -   | 320 | -   | 392 | 11 | 224 | 352 | -   | 1.42               | 45          |
| --3831-0050 | 500        | 508 | 128  | -   | -   | 320 | -   | 442 | 11 | 224 | 416 | -   | 1.58               | 45          |
| --3831-0055 | 550        | 559 | 128  | -   | -   | 320 | 416 | 492 | 11 | 224 | 352 | 448 | 1.75               | 45          |
| --3831-0060 | 600        | 610 | 128  | 224 | -   | 416 | -   | 542 | 11 | 224 | 352 | 480 | 1.91               | 39          |
| --3831-0065 | 650        | 660 | 128  | 224 | -   | 416 | 544 | 592 | 11 | 224 | 352 | 544 | 2.06               | 32          |
| --3831-0070 | 700        | 711 | 128  | 224 | 288 | 416 | 544 | 642 | 11 | 224 | 352 | 544 | 2.22               | 27          |

Order codes with this tint indicate Quick Ship lengths currently held in stock

### BOTTOM/PLATFORM MOUNT BRACKET



### BOTTOM/PLATFORM MOUNT BRACKETS

| ORDER CODE | DIMENSIONS       |       |       |       |       |       |
|------------|------------------|-------|-------|-------|-------|-------|
|            | FOR SLIDE LENGTH | A     | B     | C     | D     | E     |
| --63335    | 350              | 346.7 | 236.5 | 300.0 | 150.0 | 114.4 |
| --63340    | 400              | 396.7 | 286.6 | 350.0 | 175.0 | 139.4 |
| --63345    | 450              | 446.8 | 336.6 | 400.0 | 200.0 | 164.4 |
| --63350    | 500              | 496.8 | 386.6 | 450.0 | 225.0 | 189.4 |
| --63355    | 550              | 546.8 | 436.6 | 500.0 | 250.0 | 214.4 |



NEW TO THE  
**Accuride®**  
**QUICKSHIP**  
PROGRAMME

3831



# Accuride®

100%+ extension medium duty with disconnect and lock-out  
(minimal side-space required)



## FEATURES

- Load rating up to 68 kg
- Side space 12.7 mm
- 100%+ extension
- Slide has lock-out
- Chassis member disconnects
- Slide assembly is unhandled
- Hardware included for hard mounting
- Installation leaflet included
- See pages 31-34 for rack mounting bracket options
- Quick Ship finish available is Bright Zinc. For other finishes available see page 6

See page 6 - 'How to Order' - to select your desired finish and packaging.

| ORDER CODE    | DIMENSIONS   |             |       |       |       |       |       |       | KILOGRAMS PER PAIR |             |
|---------------|--------------|-------------|-------|-------|-------|-------|-------|-------|--------------------|-------------|
|               | SLIDE LENGTH | TRAVEL ±3.2 | A     | B     | C     | D     | E     | F     | SLIDE WEIGHT       | LOAD RATING |
| --3307-0012kt | 305          | 330         | -     | -     | 234.9 | 247.6 | 260.4 | 209.5 | 1.20               | 68          |
| --3307-0014kt | 356          | 381         | -     | -     | 285.7 | 298.4 | 311.2 | 260.4 | 1.41               | 67          |
| --3307-0016kt | 406          | 432         | -     | -     | 336.5 | 349.2 | 362.0 | 311.2 | 1.59               | 67          |
| --3307-0018kt | 457          | 483         | 177.8 | 314.3 | 387.3 | 400.1 | 412.8 | 362.0 | 1.82               | 66          |
| --3307-0020kt | 508          | 533         | 203.2 | 365.1 | 438.1 | 450.8 | 463.6 | 412.8 | 2.00               | 66          |
| --3307-0022kt | 559          | 584         | 228.6 | 415.9 | 488.9 | 501.6 | 514.4 | 463.6 | 2.23               | 64          |
| --3307-0024kt | 610          | 635         | 254.0 | 466.7 | 539.7 | 552.4 | 565.2 | 514.4 | 2.41               | 61          |
| --3307-0026kt | 660          | 686         | 279.4 | 517.5 | 590.5 | 603.3 | 616.0 | 565.2 | 2.64               | 58          |
| --3307-0028kt | 711          | 737         | 304.8 | 568.3 | 641.3 | 654.1 | 666.8 | 616.0 | 2.81               | 55          |

Order codes with this tint indicate Quick Ship lengths currently held in stock

## NOTES

- Dimensions in millimetres.
- All fixing positions must be used to achieve maximum load rating.
- It may be possible to manufacture alternative lengths to order. Contact your local Accuride representative for details.

Accuride  
reserve the right to  
alter specifications  
without notice.


NEW TO THE  
**Accuride®**  
**QUICKSHIP**  
PROGRAMME

3307



# Accuride®

## 100%+ extension slide



See page 6 - 'How to Order' - to select your desired finish and packaging.

### FEATURES

- 100%+ extension
- Slide assembly is unhandred
- See pages 31-34 for rack mounting bracket options
- See page 7 for optional features
- Quick Ship finish available is Bright Zinc. For other finishes available see page 6

| ORDER CODE  | DIMENSIONS   |             |       |       |       |       | KILOGRAMS PER PAIR |             |
|-------------|--------------|-------------|-------|-------|-------|-------|--------------------|-------------|
|             | SLIDE LENGTH | TRAVEL ±3.2 | A     | B     | C     | D     | SLIDE WEIGHT       | LOAD RATING |
| --0301-0012 | 304.8        | 326.0       | -     | 149.2 | 260.3 | 273.0 | 1.31               | 80          |
| --0301-0014 | 355.6        | 377.0       | -     | 200.0 | 311.2 | 323.9 | 1.57               | 77          |
| --0301-0016 | 406.4        | 428.0       | -     | 250.8 | 361.9 | 374.6 | 1.80               | 73          |
| --0301-0018 | 457.2        | 479.0       | 212.7 | 301.6 | 412.7 | 425.4 | 2.02               | 68          |
| --0301-0020 | 508.0        | 530.0       | 238.1 | 352.4 | 463.5 | 476.2 | 2.27               | 65          |
| --0301-0022 | 558.8        | 580.0       | 263.5 | 403.2 | 514.3 | 527.0 | 2.51               | 59          |
| --0301-0024 | 609.6        | 631.0       | 288.9 | 454.0 | 565.1 | 577.8 | 2.73               | 52          |
| --0301-0026 | 660.4        | 682.0       | 314.3 | 504.8 | 615.9 | 628.6 | 2.93               | 48          |
| --0301-0028 | 711.2        | 733.0       | 339.7 | 555.6 | 666.7 | 679.4 | 3.13               | 41          |

Order codes with this tint indicate Quick Ship lengths currently held in stock

### NOTES


- Dimensions in millimetres.
- All fixing positions must be used to achieve maximum load rating.
- It may be possible to manufacture alternative lengths to order. Contact your local Accuride representative for details.



# Accuride®

## Cable carrier

# CC5AD



## FEATURES

- Disconnects from chassis
- Ample provision for cable clamps
- Easily installed
- Can be rack mounted
- Quick Ship finish available is Bright Zinc. For other finishes available see page 6

### ORDER CODE

### Weight Per Unit

--CC5AD 0.475

Order codes with this tint indicate Quick Ship lengths currently held in stock

### NOTES

- Dimensions in millimetres.
- Not suitable for use with slides over 700mm in length.

## ORDERING GUIDELINES


This cable carrier can be manufactured to order in bulk with or without a disconnect pin. To create the appropriate order code, the material and finish prefix has to be determined (refer to page 6) and follow the guidelines below:-

|                        |             |                        |             |                        |             |                   |
|------------------------|-------------|------------------------|-------------|------------------------|-------------|-------------------|
| <b>CZ</b>              | <b>CC5A</b> | <b>CY</b>              | <b>CC5A</b> | <b>CY</b>              | <b>CC5A</b> | <b>D</b>          |
| finish<br>(see page 6) | model no.   | finish<br>(see page 6) | model no.   | finish<br>(see page 6) | model no.   | disconnect<br>pin |

Accuride®  
reserve the right to  
alter specifications  
without notice.

Accuride®  
**QUICKSHIP**  
PROGRAMME

CC5AD



### Slide Length Selection for Electronic Cabinets

- Take the distance between the mounting uprights, (DIM "A"), subtract 10 mm and select the slide length nearest to this dimension, **but not greater**.
- Select a bracket from the bracket selection table on page 32 with the amount of adjustability you require.

# Rack Mounting Accessories

## MOUNTING BRACKETS

- Mounting brackets simplify installation of Accuride slides in racks and enclosures.
- Short brackets are usually used at the front of the chassis and long brackets at the rear for added adjustability.
- Use the Bracket Selection Table on the next page to choose brackets compatible with the slide you have selected.
- All brackets are supplied in kits complete with fixing hardware.
- For each pair of slides order:
  - one pair of front brackets
  - one pair of rear brackets - short or long
  - four bar nuts
  - fillister head screws - if not included
  - you will also require 8 captive nuts (not supplied by Accuride).
- The brackets that are available via the Quick Ship Programme (prefix DZ) are packed as individual kits. If you require the kitted items to be supplied in bulk and packed separately simply change the part number prefix to CZ and drop the suffix KT.

# Bracket Selection Table


|                                                       |                                        |                     |                       | PART NUMBERS                                |                          |                          |                           |                           |
|-------------------------------------------------------|----------------------------------------|---------------------|-----------------------|---------------------------------------------|--------------------------|--------------------------|---------------------------|---------------------------|
|                                                       |                                        |                     |                       | SHORT BRACKETS                              |                          | LONG BRACKETS            |                           |                           |
| For Slide Models                                      | Mounting Slots in Brackets             | Bar Nuts            | Fillister Head Screws | Front                                       | Rear - Up To 28mm Adjust | Rear - Up To 40mm Adjust | Rear - Up To 220mm Adjust | Rear - Up To 208mm Adjust |
| <b>0201, 0204, 0301, 0307 &amp; 0305 (unrecessed)</b> | Four (57mm height)                     | DZ66020 (1 pair)    | included              | DZ63020 (1 pair)                            | DZ63030 (1 pair)         | not available            | DZ63230 (1 pair)          | not available             |
|                                                       | Three (43.7mm (1U) height)             | DZ66010 (1 pair)    | included              | DZ63060 (1 pair)                            | DZ63070 (1 pair)         | not available            | DZ63250 (1 pair)          | not available             |
| <b>3307 &amp; 3308</b>                                | Three (43.7mm (1U) height)             | included            | DZ66030 (Box of 100)  | Universal - DZ63310 (40mm adjust) (2 pairs) |                          |                          | not available             | DZ63360                   |
| <b>3607, 0531</b>                                     | Four (57mm height)                     | DZ66020 (1 pair)    | included              | Universal - DZ65020 (58mm adjust) (2 pairs) |                          |                          |                           |                           |
| <b>0305 (recessed)</b>                                | Four (57mm height)                     | DZ66020 (1 pair)    | included              | DZ63160 (2 pairs)                           | DZ63170 (2 pairs)        | not available            | DZ63270 (2 pairs)         | not available             |
| <b>0501 &amp; 0601</b>                                | Four (57mm height)                     | CZ66020 (1 bar nut) | included              | CZ65000 (1 bracket)                         | CZ65010 (1 bracket)      | not available            | not available             | not available             |
| <b>3831, 9301, 0530, 0115, 0522, 262 &amp; 330</b>    | No Brackets Available for These Models |                     |                       |                                             |                          |                          |                           |                           |




Bracket Selection

## RACK MOUNTING BRACKETS


Short Bracket




Long Bracket



4 Hole




3 Hole




## BAR NUTS

4 Hole Bar



3 Hole Bar



# Rack Mounting Brackets and Bar Nuts

## RACK MOUNTING BRACKETS

| Model Numbers                            | A Short | A Long | B 4 Hole | B 3 Hole | C    | D    | E    | F                              |
|------------------------------------------|---------|--------|----------|----------|------|------|------|--------------------------------|
| <b>0201, 0204, 0301, 0307 &amp; 0305</b> | 69.9    | 266.7  | 57.2     | 44.0     | 15.0 | 6.35 | 9.5  | 12.7 (4 Slot)<br>15.9 (3 Slot) |
| <b>0305 (recessed)</b>                   | 109.5   | 274.6  | 63.5     | 41.9     | 19.8 | 7.4  | 18.3 | 15.2                           |
| <b>3307, 3308</b>                        | 114.6   | 279.7  | 63.5     | 44.5     | 18.3 | 7.4  | 14   | 15.2                           |
| <b>3607, 0531</b>                        | 140.0   | -      | 60.0     | -        | 14.0 | 5.5  | 10   | 15.9                           |
| <b>0501, 0601</b>                        | 139.7   | -      | 70.0     | -        | 14.0 | 5.5  | 10   | 15.9                           |

### NOTE

■ Dimensions in millimetres.

## BAR NUTS

For ease of installation and adjustment of Accuride slides in racks and enclosures.

Easier than handling individual nuts when access to the slide mounting bracket is limited.


The following dimensions apply to all bar nuts:

thickness of bar nut - 3.2 mm

width of bar nut - 9.6 mm

mounting holes - 10/32 UNF

mounting holes / centre to edge - 3.6 mm



## RACK MOUNTING

# Mounting Instructions

The mounting brackets shown on the preceding pages are designed specifically for Accuride slides. Slides properly installed with correct mounting brackets will provide lasting, maintenance-free service. Illustrated is the correct orientation of the mounting screws for attaching mounting brackets to Accuride slides. To ensure proper operation of the slide, make certain that all bracket mounting screw heads are inserted so that the screw heads are inside the slides. The front bracket should first be positioned then securely fastened in place. The rear bracket screws should be left sufficiently loose to allow adjustment while fitting to the vertical rack strips.

The brackets are held in position by bar nuts, which in turn are fixed by fillister head screws fitted through appropriately positioned captive nuts in the front and rear rack strips. (Note: the captive nuts are not supplied by Accuride). These screws sink into the captive nuts so that their heads are flush with the rack strip.

During installation in the enclosure/rack, matching the alignment of the left hand and right hand slides is accomplished by installing one slide, then aligning it to the rack strips and securing the mounting screws. Then install the remaining slide, leaving the mounting screws sufficiently loose to permit horizontal adjustment. Moving the chassis in and out a few times prior to tightening the loose mounting screws will ensure proper alignment of the slides to each other and the cabinet. Any sign of binding indicates lateral stress or misalignment.