


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201140025](#)
Status: **Active**
Overview: [Brad® Micro-Change® \(M12\) Connectors](#)
Description: Micro-Change® Molded Junction Box, Top Mount, 4 Ports, LEDs for PNP sensors, with Molded PUR Cable, 10.0m Length



Series image - Reference only

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Passive Distribution Boxes
Series	120114
Comments	PNP SENSORS
IP Rating	IP68
NEMA Rating	NEMA 6
Overview	Brad® Micro-Change® (M12) Connectors
Product Name	Micro-Change® (M12)
UPC	78678800821

Physical

Bus I/O	Micro-Change® (M12)
Cable Connector Orientation	Straight
Cable Length	10.0m
Home Run Cable Length	10.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	Single
LED Indicator	Yes
Material - Cable Jacket	PUR
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Orientation	Top Mount
Poles	5
Poles (wired)	4
Ports	4
Temperature Range - Operating	-20°C to +90°C
Wiring Configuration	Single I/O per Port

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	Parallel
Voltage - Maximum	10-30V DC

Material Info

Engineering Number	BTY401P-FBP-10
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-120114-002
---------------	---------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120114](#) Series