



images for illustrative purposes only

## Description:

1U 19" Horizontal mount PDU offering 6 x UK BS1363 13Amp sockets. Unit features 10Amp rated RFI filter, neon switch with protective cover, 3 metre lead to 10Amp fused UK BS1363 13Amp plug, and is finished in black.

## Key Features:

### Electrical

Socket type & quantity - output  
Switch  
Power-on indicator  
Plug - power input  
Lead - type & length  
Type  
Voltage  
Amps  
Frequency  
Circuit Protection

6 x UK BS1363 sockets  
Neon double pole switch with cover  
via illuminated switch  
BS1363 13Amp (10A fuse)  
3 metre x 1.5mm<sup>2</sup> H07 RNF  
Single phase  
230V  
10A  
50/60Hz  
10Amp fused plug

### Environmental

Operating temperatures

0 - 45° C

### Physical:

Size (Dimensions H x W x D)  
Construction  
Colour - RAL  
Texture  
Unit weight  
Packaged Unit (H x W x D)

44mm x 483mm x 50mm  
Powder Coated Rolled Steel  
Black - RAL 9005  
Fine  
1.6kg  
100mm x 520mm x 100mm

## Physical Cont:

Fixing

Fixing kit included

Warranty

Three Years

Certifications

CE, RoHS, IEC60950-1

## Technical Drawing:

All measurements shown in millimetres

