



Leah

Leah is an attractive circular IP65 robust polycarbonate luminaire available for wall or ceiling mounting.

Leah offers a choice of 2D, T5c and TC-S energy-saving lamps for mains lighting with optional integral 3 hour emergency versions including slave.

Supplied as standard with a hinged geartray, white base and opal diffuser, this high quality elegant luminaire provides a reliable and effective solution for most indoor and outdoor applications.

Leah with large white trim



Optional elegant trims are available which create an impressive diffused halo-effect enabling this stylish range of luminaires to be considered for luxurious or challenging applications including hotels, universities, shower areas and stairwells.

Alternatively, the Leah can be used as a semi-recessed luminaire when using the narrower version of the two attractive trims.

Leah is suitable for self-test emergency lighting and can be supplied with emergency gear for intelligent addressable systems.

Leah with narrow white trim



Mains Luminaires

Cat No.	Lamp	Lumens	Kg
LE28	28W 2D	-	2.70
LE38	38W 2D	-	2.70
LE40	40W T5c Circular	-	2.70
LE211	2 x 11W TCS	-	2.70

Emergency Luminaires

Cat No.	Mode/Lamp	Lumens*	Kg
LE28/M3	M3 28W 2D	384	3.60
LE38/M3	M3 38W 2D	625	3.60
LE40/M3	M3 40W T5c Circular	370	3.60
LE211/M3	2 x 11W TC-S (One lamp in M3)	390	3.60

Slave Luminaires

Cat No.	Mode/Lamp	Lumens*	Kg
LE28/#D	Slave 28W 2D	500	2.60
LE38/#D	Slave 38W 2D	500	2.60
LE40/#D	Slave 40W T5c Circular	990	2.60
LE211/#D	Slave 2 x 11W TCS	380	2.60

* Emergency Lumens

Specify 24, 50, 110 or 230 Volts AC/DC System Voltage

* For other durations, specify the required time period e.g. /M3 becomes /M1 for 1 hour duration

No Trim Version Dimensions: Ø 395mm x 120mm

Narrow Trim Version Dimensions: Ø 440mm x 120mm

Broad Trim Version Dimensions: Ø 520mm x 120mm

Recess Cut out: Ø 357mm

Options Suffix:

/ST	Self Testing Luminaire
/AD	Intelligent Addressable luminaire
/HF	High Frequency
/NT	Narrow Trim
/WT	Wide Trim
/OP	Opal Halo Base