






Copyright FCI.




PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Core range						
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	G±0.25	PART NUMBER
09	30.81	24.99	16.96	16.79	5.90	D09P13A4GX00**
15	39.14	33.32	25.18	25.12	5.90	D15P13A4GX00**
25	53.03	47.04	39.12	38.84	5.70	D25P13A4GX00**

GENERAL CHARACTERISTICS - SEE DRAWING C01-8646-0000

LF FOR LEAD FREE



rev	ecn no	dr	date
J	I05-0124	JS	2005/07/27
K	I06-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOHN SLEEBA	1994/08/01	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1:1		
Eng	GEORGE VJ	1994/08/01			0.XX	±0.1				
Chr	GEORGE VJ	2005/07/27			0.XX	±1°				
Appr	KVSD	2005/07/27	Product family				D-SUB	Spec ref -		
			title MALE CONNECT.DELTA D RIGHT ANGLED WITH NUT, HARPOON & METAL PLATE.				dwg no C01-8646-0281-1		Rev. K	
catalog no DELTA-D										
			CUSTOMER				sheet 1 of 1			

REV F - 2006-04-17