

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929




SWITCH — BASIC

CATALOG LISTING
V7-2B17P07-207-1

CW-B3059

CATALOG LISTING
V7-2B17P07-207-1
REPLACES
RELEASE NO. PR-19128
ISSUE
2

REVISIONS
A CO 76214
GRT 20 OCT 93
JAL 16 MAY 91
WJC 13 MAY 91
DDM/CAD
DRAWN




NOTES
1 — TERMINALS ARE SILVER PLATED FOR SOLDERING

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 43 GRAMS MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 3 GRAMS MIN	L156 11A 1/3HP 125, <u>250</u> OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L" 	ONE PLACE (.0)	± .030
DIFFERENTIAL TRAVEL — — — .025 MAX		TWO PLACE (.00)	± .015
OVERTRAVEL — — — — — .060 MIN		THREE PLACE (.000)	± .005
RELEASE TRAVEL — — — — — .016 MIN		ANGLES	±
		WEIGHT	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-2B17P07-207-1](#)