



1

2



3

4

5



PCB LAYOUT



Poles	A
2	5.08
3	10.16
4	15.24
5	20.32
6	25.40
7	30.48
8	35.56
9	40.64
10	45.72
11	50.80
12	55.88

CHARACTERISTICS

MATERIAL

Insulator material : LCP

Flammability rating : UL94-V0

Colour : Black

Contact pin : Brass (CuZn)

Surface of solder tail plating : Tin Plated

ENVIRONMENTAL

Operating temperature : -40°C up to 105°C

Compliance : Lead free and RoHS

SOLDERING

Solder temperature : Reflow process as per JEDEC J-020D-STD

ELECTRICAL

Current rating : 10A

Working voltage : 300 Vac

Dielectric withstanding voltage : 4 kVac/min

Contact resistance : 20 mΩ max

STANDARD

cULus Certified : E315414 / Model number 7015

MECHANICAL

Pitch : 5.08mm

PACKAGING

Tape & Reel

RoHS Compliant

G

F

E

D

C

B

A

REV

19-DEC-11

14-SEP-11

DATE

6917015300xx

PDF


FILE

QL

QL

BY

PROJECTION:



APPROVAL: RJ

GENERAL TOLERANCE

.X = ± 0.2 .XX = ± 0.15

UNIT: MM

SCALE: 2/1

SHEET: 1/2

DRAW: QUENTIN



DESCRIPTION: SERIE 7015B - 5.08MM OPEN HORIZONTAL PCB HEADER - THR TYPE

WERI PART NO: 691 701 530 0xx B

SIZE

A4

