

PERFORMANCE
1/8" CUT, 1/32" SPACE TYP.
2.00" REPEAT.

1.000 [25.40]

.750 [19.05]

2.000 [50.80]

.500 [12.70]
TYP. 12 PLCS.

.800 [15.24]
TYP. 11 PLCS.

8.1 [205.74]

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	LABELS PER ROW	ROWS PER FANFOLD	STANDARD PKG. QTY.
N050X075CBD	GMC	0.500 (12.7) X 0.750 (19.1)	12	12	5000

O	10-1-04	RVU		DRAWING RELEASED.		0000	R			
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	

PANDUIT CORP. TINLEY PARK, ILLINOIS

OPTIMUM N050X075CBD
COMPUTER PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .031 (.XXX) ± .005
(.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU	
-----------------	--

	MAT'L;
--	--------

SCALE 1/2

DATE	10-1-04
------	---------

AS NOTED

DRAWING NO.

C10280

DWG
A
SIZE