



LOC		DIST		REV		REVISIONS		DATE		APPD	
6	14	P	P	ZONE	LTR	DESCRIPTION					
						B	REVISED PER 0720-0230-93		2/25/94		W.D.

METRIC
DIMENSIONS LISTED IN mm [INCHES]



AMP WIRE RANGE		E13288 Listed	
22-16 AWG STRANDED		22-16 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE: 170°C MAX

VOLTAGE RATING:

NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP AND ITS CUSTOMERS. IT IS SUBJECT TO CANCELLATION
AND REVISIONS WITHOUT NOTICE. THE LATEST REVISION
SHOULD BE CONSULTED FOR THE LATEST REVISION.

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN - - - - - INCHES - - - - -
TOLERANCES ON:
2 PLG DEC ± - -
3 PLG DEC ± - -
ANGLES ± - -
MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [L.0001001] MIN
THK PER MIL-T-10727

DR 1-27-93
TA BRINKMAN
CHK 1-27-93
DA PATTERSON

APPD 1-27-93
DE MILLER

APPD 1-27-93
JL MECKLEY

PRODUCT SPEC

APPLICATION SPEC



AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
BUDGET

SIZE CAGE CODE DRAWING NO
C 00779 C-31090

SCALE 10:1 SHEET 1 OF 1

CUSTOMER DRAWING