



4. Magnetic Shielded Type SA

■ Type 3225(1210)SA

● Dimensions in mm (not to scale)



● Recommended Land Pattern in mm (not to scale)



■ Standard Packing Quantity

● 2000 pcs./1 reel

■ Examples

Part No.	Inductance			Q		SRF * ¹ (MHz)min.	DCR * ² (Ω)max.	DC Current (mA)max.	
	(μH)	Freq. (MHz)	Tolerance	min.	Freq. (MHz)				
ELJSA100KF	10	1.0	±10 %	40	5.0	30	1.8	18	
ELJSA120KF	12					28	2.0	17	
ELJSA150KF	15					25	2.2	15	
ELJSA180KF	18					23	2.5	13	
ELJSA220KF	22					20	2.8	12	
ELJSA270KF	27					18	3.2	10	
ELJSA330KF	33					17	3.5	10	
ELJSA390KF	39					15	3.8	9	
ELJSA470KF	47					14	4.0	8	
ELJSA560KF	56					13	4.5	7	
ELJSA680KF	68					1.5	12	5.0	6
ELJSA820KF	82						11	6.0	6
ELJSA101KF	100	10		7.0	5				
ELJSA121KF	120	9		8.0	5				
ELJSA151KF	150	5		9.0	5				
ELJSA181KF	180	5		11.0	5				
ELJSA221KF	220	4		12.0	5				
ELJSA271KF	270	4		14.0	5				

*1 : Self Resonant Frequency *2 : DC Resistance