






REV.	DATE	DESCRIPTION
NC	06/27/98	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.						05/01/04			
7						CHECKED								PART DESCRIPTION SMA BULKHEAD CRIMP JACK (FOR RG-8/X, LMR-240)		
6	FERRULE	COPPER	GOLD	1		ISSUED			PART NO. 132241							
5	HEX NUT	BRASS	GOLD	1		SHEET	1 OF 1						DWG. NO. 132241.DWG REV. A SIZE A SCALE NA			
4	LOCK WASHER	BRASS	GOLD	1												
3	CONTACT PIN	BER. COPPER	GOLD	1												
2	INSULATOR	TEFLON	NATURAL	1												
1	BODY	BRASS	GOLD	1												
DESCRIPTION		MATERIAL	FINISH	QTY												