






PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-.01 [7.56]
1.25-2.0 [0.049-.079]	19.4-.01 [7.64]
2.0-3.0 [0.079-.118]	19.8-.01 [7.80]



SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
1-1a	OPEN



CIRCUIT: SPST


NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4

$$X.XX=\pm 0.25$$

3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC

5. MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles



E-SWITCH®

TITLE				
R1966A BLK BLK EF				
C	11664	REVISED PART DESCRIPTION	9/18/01	CJB
REV.	ECN NO.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE		DATE	DR	DWG
1.5:1		9/18/01	CJB	M300000
				REV
				C