

GPS450

Window Mount GPS Antenna

Features

- ◆ Active GPS Antenna
- ◆ Window Mount
- ◆ Discrete Design
- ◆ Ideal for fleet applications

Specifications

Specifications	
Frequency	1575.42
Polarisation	RHCP
LNA gain	25 dB
Noise Figure	2.0 dB max
Voltage	3V
Power Consumption	20 mA (max)
Cable / Connector	3M RG-174 and SMA-Male
Dimensions	45x45x14.5mm

Ordering Options

Ordering Options	
FGPX35135-SM-3K	GPS 450 with 3M RG-174 and SMA-Male

www.ead-ltd.com

Specifications subject to change without notice.

Unit 19, Hillcrest Way
Buckingham Industrial Park
Buckingham
MK18 1HJ
UK

Tel: +44 (0)1280 825537
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com


EAD
embedded antenna design ltd



GPS450 | Window Mount GPS Antenna

Return Loss

Outline Drawing



Specifications subject to change without notice.

Unit 19, Hillcrest Way
Buckingham Industrial Park
Buckingham
MK18 1HJ. UK

Tel: +44 (0)1280 825537
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.co.uk