





- NOTES:
1. MATERIAL : BRASS
 2. FINISH : HOT TIN DIP, THICKNESS 0.51 MICROMETER MIN
 3. PIN TERMINALS FOR USE WITH THE .084/(2.13) SERIES HOUSINGS.
PLUG (42021-**)
CAP (42022-**)
PIN TERMINAL TO MATE WITH SOCKET TERMINALS OF .084/(2.13) DIA SERIES
 4. CRIMP RANGE SEE CHART
 5. PRODUCT SPECIFICATION : PS-36663-001 APPLIES



TERMINALS IN CHAIN FORM
SCALE 1:1

MATERIAL No.	FINISH	WIRE SIZE	INSULATION DIA	PACKAGING
36663-0001	SEE NOTE 2	10-12AWG	5.08 MAX	REEL
36663-0002	SEE NOTE 2	10-12AWG	5.08 MAX	LOOSE

EC NO: 12005-0004 DRWN:SSUDHIR 2004/07/07 CHKD:DGDATHA 2004/07/07 APPR:DGDATHA 2004/07/08 1	DESCRIPTION REV	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY			
				mm	INCH	DIMENSION STYLE MM ONLY		TITLE STAMP PART BRASS TERMINAL SPLIT PIN MLX 10-12AWG 5.08 INS DIA MOLEX INCORPORATED			
			4 PLACES	± ---	± ---	DRAWN BY	DATE				
			3 PLACES	± ---	± ---	SSUDHIR	2004/07/01				
			2 PLACES	± 0.25	± ---	CHECKED BY	DATE				
				1 PLACE	± 0.38	± ---	DGDATHA	2004/07/01	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-36663-001	SHEET NO. 1 OF 1
			ANGULAR ± 2 °		APPROVED BY		DATE				
			DRAFT WHERE APPLICABLE		DGDATHA		2004/07/01				
			MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
					B						