

Direct Mount Terminals Feed Through


Technical Data

Voltage Rating
Current Rating
Wire Size
Strip Length
Torque
Number of poles
Molding Material

Terminal Strips

Cut offs

EKS 12/4



UL

300V

20A

#22...12

5(.20")

.9(8.0)

12

Polyamide (white)

Type

EKS 12/4

126(4.96")

62350

12-poles

2-poles

3-poles

4-poles

5-poles

6-poles

7-poles


8-poles

9-poles

10-poles

11-poles

MK 3



UL

300V

20A

#22...12

5(.20")

.9(8.0)

12

Melamine

Type

MK3/12

109.9(4.33")

24352

MK3/12

109.9(4.33")

24352

MK3/2

17.95(.707")

27382

MK3/3

27.20(1.07")

27392

MK3/4

36.45(1.44")

27402

MK3/5

45.70(1.80")

27412

MK3/6

54.95(2.16")

27422

MK3/7

64.20(2.53")

27432

MK3/8

73.45(2.89")

27442

MK3/9

82.70(3.26")

27452

MK3/10

91.95(3.62")


27462

MK3/11

101.2(3.98")

27472

MK 3



UL

300V

20A

#22...12

5(.20")

.9(8.0)

12

Polyamide

Type

MK3/12

109.9(4.33")

24356

MK3/12

109.9(4.33")

24356

MK3/2

17.95(.707")

27386

MK3/3

27.20(1.07")

27396

MK3/4

36.45(1.44")

27406

MK3/5

45.70(1.80")

27416

MK3/6

54.95(2.16")

27426

MK3/7

64.20(2.53")

27436

MK3/8

73.45(2.89")

27446

MK3/9

82.70(3.26")

27456

MK3/10

91.95(3.62")


27466

MK3/11

101.2(3.98")

27476

MK 6



UL

300V

30A

#22...10

9(.35")

2.3(20)

6

Melamine

Type

MK 6/6

74.90(2.95")

62012

MK 6/2

24.45(.963")

62042

MK 6/3

37.45(1.47")

62032

MK 6/4

50.45(1.99")

62022

MK 6/6

75.50(2.99")


62012

BSTb

17/6

30460

MK 6



UL

300V

30A

#22...10

9(.35")

2.3(20)

6

Polyamide

Type

MK 6/6

74.90(2.95")

62016

MK 6/2

24.45(.963")

62046

MK 6/3

37.45(1.47")

62036

MK 6/4

50.45(1.99")


62026

BSTb

17/6

30460

MK 10*



UL

150V

25A

#22...12

6(.24")

.45(40)

14

Polyamide

Type

MK10/14

88.5

37016

MK10/2

25.28(.995")

44866

MK10/3

31.61(1.24")

44876

MK10/4

37.93(1.49")

44886

MK10/5

44.25(1.74")

44896

MK10/6

50.57(1.99")

44906

MK10/7

56.89(2.24")

44916

MK10/8

63.21(2.49")

44926

MK10/9

69.54(2.74")

44936

MK10/10

75.86(2.99")

44946

MK10/11

82.18(3.24")

44956

MK10/12

88.50(3.48")

44966

Mounting holes provided

on cutoffs only

*Can be mounted using glue or with M3 x 12 screws through the terminal screw hole. Cutoff versions provide mounting holes.