

TL75 -1 Hard Point TM Test Lead Set



Overview

Models and Accessories

Knowledge and Information

- One pair (red, black) of comfort grip probes
- 48 inches (1.22 meter) PVC insulated test leads with right-angle shrouded banana plugs
- Recommended for general purpose measurements
- CAT II 1000 V, 10 A rating EN/IEC 61010-031:2002 +A1:2008
- One year warranty

TL220 -1 SureGrip™ Industrial Test Lead Set



Overview

Models and Accessories

Knowledge and Information

Handy all-in-one kit that includes :

- AC220 SureGrip™ Alligator Clip Set
- TP238 SureGrip™ Insulated Test Probe Set
- TL222 SureGrip™ Silicone Test Lead Set (right to right)
- One year warranty



TL223 -1 SureGrip™ Electrical Test Lead Set



Overview

Models and Accessories

Knowledge and Information

Handy all-in-one kit that includes :

- AC220 SureGrip™ Alligator Clip Set
- TP238 SureGrip™ Insulated Test Probe Set
- TL224 SureGrip™ Silicone Test Lead Set (straight to right)
- One year warranty



TLK-225 -1, SureGrip™ Master Accessory Set



Overview

Models and Accessories

Knowledge and Information

Kit includes all the SureGrip™ leads and probes in a handy 6-Pocket roll-up pouch:

- AC220 SureGrip™ Alligator Clip Set
- AC280 SureGrip™ Hook Clip Set
- AC283 SureGrip™ Pincer Clip Set
- AC285 SureGrip™ Large Jaw Alligator Clip Set
- TP238 SureGrip™ Insulated Test Probe Set
- TL224 SureGrip™ Silicone Test Lead Set

T5-KIT-1, T5 Tester Accessory Starter Kit



Overview

Models and Accessories

Knowledge and Information

Special value starter kit for the electrical professional who already owns a Fluke T5 Electrical Tester or is thinking of buying one. Includes insulated test probes, alligator clips for hands free connections and a soft carry case to protect your tester when not in use and store your accessories. Included with kit:

- TP238 SureGrip™ Insulated Test Probe Set
- AC285 SureGrip Large jaw alligator clips
- C33, soft carrying case

TL80A -1, Test Lead Set, Basic Electronic



Overview

Models and Accessories

Knowledge and Information

- Economical accessories for making measurements in low energy, electronic applications
- One pair (red, black) each 1 meter long WearGuard™ test lead set, TL71-1. Exposes contrasting color when leads are damaged and need replacing.
- Compatible with all instruments that accept standard 4 mm, shrouded banana connectors
- EN/IEC 61010-031:2002 +A1:2008
- Includes: Alligator Clips, 5 A max Insulated Extended probe tips, 3A max
- C75 soft carrying case
- One year warranty

TLK282 -1, Deluxe Automotive Test Lead Kit



Overview

Models and Accessories

Knowledge and Information

Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. Use the back probe pins to slide into weather pack connectors on fuel injectors, TPS and MAP sensors. A hook probe with plunger actuation allows quick connection to pins or exposed conductors.

- Tested to 60 V DC

Kit contains:

- TP81 Insulation Piercing Clip Set
- TP40 Automotive Back Probe Pins (five)
- TL224 Suregrip™ Silicone Test Lead Set
- TP238 SureGrip™ Insulated Test Probe Set
- AC220 Suregrip™ Alligator Clip Set
- AC285 Suregrip™ Large Jaw Alligator Clip Set
- AC280 Suregrip™ Hook Clip Set
- Soft Case, 6-Pocket roll-up pouch

VPS40-III Voltage Probe, 10:1, with safety-designed shrouded 4mm testpin

Overview

Models and Accessories

Knowledge and Information

Voltage Probe, 10:1, with safety-designed shrouded 4mm testpin, for use with 120 Series ScopeMeter®. Hook clip and ground lead included. The shrouded 4mm banana testpin makes this probe also compatible with standard safety-designed alligator clips (like e.g. the AC285).

Set contains 600 V CAT III / 1000 V CAT II rated items:

- 10:1 Voltage Probe, 1 Black
- Hook Clip, 1 Red (HC120-III)
- Ground Lead with Mini Alligator, 1 Black

Specification:

- Attenuation 10x
- Bandwidth DC to 40 MHz (-3 dB)
- Max Input Voltage 600 V CAT III / 1000 V CAT II as per IEC61010-031:2008
- V*Hz product: 500*10⁶ V*Hz
- Max Floating Voltage: See Instrument Manual
- Input Resistance / Capacitance, 5 MΩ // 15.5 pF
- Compensation Fixed for ScopeMeter 120 Series (14 pF)
- Probe Tip: safety-shrouded 4 mm banana pin with test tip (see photo)
- Instrument Connector 4 mm shielded banana plug
- Cable Length 1.2 m
- Safety IEC / EN 61010-031:2008; UL61010 B-2-031; CSA C22.2 No. 1010.2-031
- Working Voltage 600 V CAT III / 1000 V CAT II
- Pollution Degree 2
- Protection Class II (double insulation)

