


REV.	DATE	DESCRIPTION
NC	12/11/97	INITIAL RELEASE
A	01/08/07	REVISE DESCRIPTION, UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.								01/08/07
7						CHECKED			PART DESCRIPTION BULKHEAD CABLE TERMINATOR (FOR RG-174/U, 316/U CABLE)						
6						ISSUED									
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		PART NO. 142207						
4	HEX NUT	BRASS	NICKEL	1											
3	LOCK WASHER	BRASS	NICKEL	1				DWG. NO. 142207.DWG							
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	NICKEL	1				REV.	A	SIZE	A	SCALE	NA		
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/142/142207.DWG								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142207](#)