

NetCommander 19" VGA Console Cat5 KVM Switch - 16 Port

MODEL NUMBER: **B070-016-19**



Description

Tripp Lite's B070-016-19 NetCommander Rackmount Console KVM switch is a cost effective and highly flexible system for controlling up to 256 computers from a single 19" display console. This console can be cascaded with Tripp Lite's stand-alone B072 NetCommander series KVM switches. Switching between attached servers can be accomplished via the On Screen Display (OSD) menu or Hotkey commands. Utilizing Tripp Lite's B078-101-Series server interface units, KVM cabling is kept to a minimum via inexpensive Cat5/5e/6 patch cables. Servers can be located up to 100 ft. away from the switch. Password feature provides additional security to prevent unauthorized access to attached computers. All rackmount hardware is included, and is designed for easy, one person installation. Fits into any rack from 27" to 42" deep. 2-post rackmounting available using Tripp Lite's B019-000. Compatible with all major operating systems. Constructed of heavy-duty steel housing.

Features

- 16-port Cat5 KVM Switch with built-in 19" Monitor, Keyboard, and Mouse
- Supports resolutions up to 1366 X 768
- Connect and control up to 256 computers locally or remotely
- Standard EIA 19" rackmounting
- Use in racks from 27" to 42" deep
- OSD menu for intuitive operation and easy control
- USB and PS/2 mouse/keyboard support
- Password protection and auto-logout features
- Firmware upgradeable
- Hot-swappable: disconnect and reconnect USB computers w/o reboot
- Easy port selection via On Screen Display (OSD) or Hotkey commands
- Rugged ball bearing slides offer long life usage
- Uses readily available Cat5/5e/6 patch cables to locate computers up to 100 ft. from the KVM
- IP upgradeable using Tripp Lite B051-000 IP Remote Unit

Highlights

- 16-port Cat5 KVM Switch with built-in 19" Monitor, Keyboard, and Mouse
- Expandable: Connect and control up to 256 computers
- Compatible with all major operating systems

System Requirements

- PS/2 or USB computer / server
- (1) [B078-101-PS2](#) (PS/2) or [B078-101-USB](#) (USB) Server Interface Unit is required for each connected computer/server
- Compatible with all major operating systems

Package Includes

- B070-016-19 16-port KVM 19" Console
- Power Cord
- Serial Firmware Upgrade Cable
- KVM/Console Jumper cable
- Owners manual CD



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
# Of Users	1
Console	Yes
Port Control	Hotkeys, OSD
Max CPU	256
PC/Server	PS/2
Cat5 KVM Switch	Yes
IP Remote Access	No
INPUT	
Electrical Consumption	(Line Mode) 30W / (Standby Mode) 5W
Nominal input voltage description	Internal Switching 100-240 VAC 50/60Hz
PHYSICAL	
Unit Dimensions (HWD/in)	1.7" x 19" x 26.8"
Unit Dimensions (HWD/cm)	4.32 x 48.26 x 68.07
Unit weight (lbs)	36.0
Unit weight (kg)	16.33
Color	Black
Style	1U Rackmount Console
LCD Monitor (in.)	19
LCD Monitor (cm)	48.26
ENVIRONMENTAL	
Storage Temperature Range	-40F to 158F
Relative Humidity	80% Non-condensing Relative Humidity
Operating Temperature	32F to 104F
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.06 BTU/Hr
CONNECTIONS	
Ports	16
Computer/Server Ports	16 x RJ45



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Firmware Upgrade Port	RJ45
FEATURES/SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	Variable
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

Related Items

Required Products

Model Number	Description	Qty.
B078-101-PS2	KVM Switch Accessories - NetCommander PS2 Server Interface Module	1
B078-101-USB-1	KVM Switch Accessories - NetCommander USB Server Interface Module	1

Optional Products

Model Number	Description	Qty.
N201-010-GY	10-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
N201-014-GY	14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
N201-025-GY	25-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
B051-000	IP Remote Access Unit (KVM over IP)	1
B019-000	KVM Switch Accessories - 2-Post Rackmount Bracket for B020,B021, B040, and B070 Consoles and KVM Consoles	1
B070-008-19	NetCommander 19" VGA Console Cat5 KVM Switch - 8 Port	1
B070-016-19-IP	NetCommander 19" Console w/ 16-Port Cat5 IP KVM Switch	1
B072-008-1	KVM Switch - 8-Port NetCommander 1U Rackmount Cat5 KVM Switch	1
B072-016-1	KVM Switch - 16-Port NetCommander 1U Rackmount Cat5 KVM Switch	1
B072-016-1-IP	KVM Switches- 16-Port NetCommander 1U Rackmount Cat5 KVM Switch w/IP	1
WEXT-KVM-B1	1-Year Warranty Extension - For select KVM Switches (see specific models for eligibility)	1
WEXT-KVM-B2	2-Year Warranty Extension - For select KVM Switches (see specific models for eligibility)	1
WEXT-KVM-B3	3-Year Warranty Extension - For select KVM Switches (see specific models for eligibility)	1
WEXT-KVM-B4	4-Year Warranty Extension - For select KVM Switches (see specific models for eligibility)	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/B070-016-19>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B070-016-19](#)