


T- Flash Card Connector Push Push Type



Material:

Housing: High Temperature Plastic UL94V-0.

Contacts: Copper Alloy.

Shell: Metal

Electrical Characteristics:

Current Rating: 0.5 A.

Dielectric Withstanding Voltage: AC 500V .

Insulator Resistance: 1000M Ω min.

Contact Resistance: 40mΩ max.


Operating Temperature: -25°C~+85°C.

Features:

* Ultra small for space saving.

* Top Mount.

Mates with: T- Flash Card.



Ordering information

9004-

Series

BN

T- Flash
Card Style

09

Position

B

B: Black

G

G: Gold Plated

10

$$\overline{10:10 \mu''}$$

A

A: Top Mount Type

T

T: Tape & Reel Package
U: Tube Package