


HONEYWELL
PART NUMBER

590-33AA33-503

REV	DOCUMENT	CHANGED BY	CHECK
E	0023729	CH 14AUG06	RK



CONNECTOR	AMP PART No. 104257-1
RECEPTACLES (2)	AMP PART No. 103358-4
LEADWIRES (2)	28 AWG, TEFLON INSULATED
HOUSING	ALUMINUM
THERM. CURVE, MAT'L	1, Q

ALL DIMS. NOM. UNLESS OTHERWISE NOTED.

RoHS Compliant

RESISTANCE (OHMS)

TEMP °C	MINIMUM	NOMINAL	MAXIMUM	REF	TOL
0	173,617	175,500	177,405	±0.2°C	
25	49,535	50,000	50,470	±0.2°C	
70	7,693.2	7,750	7,807.2	±0.2°C	

DESIGN UNITS:	INCH
TOLERANCES UNLESS NOTED:	
NO PLACE	X ±
ONE PLACE	.X ±
TWO PLACE	.XX ±
THREE PLACE	.XXX ±
FOUR PLACE	.XXXX ±
ANGLES	X ±

THIRD ANGLE PROJECTION



DRAWN	CH	14AUG06
CHECK	RK	14AUG06

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

Honeywell

TITLE				PROBE ASSEMBLY OUTLINE	
SIZE	TYPE	DRAWING NAME	REV		
B	I	590-33AA33-503	E		
AUTOCAD	2D	SCALE	NTS	SHEET	1 OF 1