






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

PANDUIT PART NO.	BUNDLE DIA MIN - MAX.	DIMENSIONS				MATERIAL	COLOR	WEIGHT grams 100 pcs
		'A'	'B'	'C'	'D'			
HCME06A12-...20	6 - 12	1.2	15	12.0	10.0	NYLON 6/6	BLACK	150
HCME06A12-..130	6 - 12	1.2	15	12.0	10.0	ACETAL		



Application
Specification
Detail View
(See note 3)



SCALE: FULL

NOTES:

1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
3. APPLICATION SPECIFICATION:
PUNCHED RECTANGULAR HOLE: 4.0 x 11.0 mm
PANEL THICKNESS: 0.6 - 1.2 mm

CAD FILENAME/LAYERS		10B0151X_DC/00 - GB1932BF_REV08							
PANDUIT		CORP.		TINLEY PARK, ILLINOIS					
HARNESS CLIP FOR EDGE MOUNT									
Unless otherwise specified, all dimensions are metric tolerance; ±0.5mm									
DRAWN BY		JAD		SCALE		2X			
DATE		5-7-98		SEE TABLE		DRAWING NO.		DWG	
CHK'D						GB1932BF		A	
								SIZE	

OB	3/20/13	BWG	JADE	REVISED DIMENSION "D" WAS 9.7 - 9.7. CAD FILE WAS G01932BF_PB_HCME06A12_07. REVISED NOTE 1.	GB1932BF	OB		PBC	
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		