

PRODUCT DATASHEET

Pro 6 LED Headlight *Energizer*

HDL33A2E

HANDS-FREE

- Light where you need it without having to hold it
- Swivel adjustment aims light



VERSATILE

- Spot, flood and area lights plus night vision LEDs
- Push button switch cycles modes



ECONOMICAL

- Runs 18 hours on one set of batteries in high mode
- LEDs never need replacing



BRIGHT

- Provides 46 lumens of light in high mode
- Uses premium Nichia® LED technology.



Lightweight, versatile and comfortable, the Energizer® Pro 6 LED Headlight is perfect for electrical, plumbing, HVAC or other work that requires both hands. It puts light where you are looking and has a swivel adjustment with ratchet positioning for accurate aim.

Variable light sources allow you to choose the best illumination for the job – area, flood, spot or night vision. Also, this light mounts securely to hard hats or can be comfortably worn around the head for long periods of time.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation: Energizer
Pro 6 LED Headlight
Model: HDL33A2E
Color: Orange
Power Source: Three "AAA"
ANSI/NEDA: Series 24
Lamp: Four White LEDs, Two Red LEDs
Lamp Life (hr): Lifetime

Mode:	4 White	2 Spot	2 Flood	Red
Lamp Output (lumens):	46	28	29	4
Run Time (h:mm):	18	28	27	24:45
Beam Distance (m):	33	29	22	N/A*
Peak Beam Intensity (cd):	272	210	121	N/A*

* Beam Distance and Peak Beam Intensity are not applicable to colored LEDs


Weight: 80 grams with batteries

Dimensions (mm): 45 x 40 x 73

Performance:

Run Time

Continuous Drain to
End of Useable Light (21° C)



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved