

Conductor marking collar - LBHZ 3/WH:UNBEDRUCKT - 1013562

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marking collar, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Slide on, Cable diameter: 2.5-47 mm, Lettering field: 5.5 x 10 mm

Key commercial data

Packing unit	1 PCE
Minimum order quantity	100 PCE
GTIN	 4 017918 013844
Weight per Piece (excluding packing)	1.38 GRM
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Height	7 mm
Width (a)	5.5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	10
Number of individual labels per row	10

Conductor marking collar - LBHZ 3/WH:UNBEDRUCKT - 1013562

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410