


RNF100




Dimensions (in millimetres)

Part Number	Inside Diameter		Wall Thickness
	D (min) Expanded as supplied	d (max) Recovered after heating	W (nom) Recovered after heating
RNF100 NR.541	6.0	1.6	0.5
RNF100 NR.610	5.3	1.6	0.5

RNF 100 NR. 541 Available in colours only (not clear)

RNF 100 NR. 610 Available in colours and clear.

Issued by



Issue 2

Date

7 March 1978

Approved by

