




Material and Finish

Body: PBT Thermoplastic
UL94V-0 rated
color - Pantone 701C (Pink)

Cover: PBT Thermoplastic
UL94V-0 rated
color - Pantone 701C (Pink)

Bushing: Brass, Nickel Plated
Bushing Sleeve: PBT, Pink

Terminals and Contacts: Phosphor Bronze
Coil Springs: Spring Steel

Mechanical Characteristics

Insertion Force: 0.4kg - 3.0kg

Extraction Force: 0.3kg - 3.0kg

Durability: 5000 Mating Cycles

Electrical Characteristics

Contact Rating: 0.3 amps at 16V DC


Insulation Resistance: 100 Megohms
min. at 500V DC

Contact Resistance:
Before Durability Test
To Terminals: 30 milliohms Max.
To Sleeve: 50 milliohms Max.
After Durability Test
To Terminals: 60 milliohms Max.
To Sleeve: 100 milliohms Max.


Dielectric Strength: 500V AC RMS
for one minute

Operating Temp: -25°C to +80°C

PCB LAYOUT (BOTTOM VIEW)



REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	03/07/00	New Drawing	K. Wallace	K. Wallace	K. Wallace	03/07/00
A1	12/01/00	Modify Dims.	K. Wallace	K. Wallace	K. Wallace	
A2	03/20/02	ECO#01-025	M. Yiu	K. Wallace	K. Wallace	
A3	4/8/02	ECO#01-128	C. Leiva	C. Leiva	C. Leiva	
A4	6/7/02	ECO#02-043	C. Leiva	C. Leiva	C. Leiva	
R1	8/29/05	ECO#05-037	R. Aquirre	H. MA	H. MA	



ST-3150-5N-701C

Stereo Jack, 3.5mm, 5 POS, Non-Threaded

Slim Design With Switch, Pink PC99



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[ST-3150-5N-701C](#)