









NOTE:
MATERIAL:
HOUSING:PBT+30%G.F. UL 94V-0
CONTACT 5P:BRASS
CONTACT 4P:PHOSPHOR BRONZE
SHELL:BRASS
PLATING:
CONTACT: GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL: NICKEL PLATED OVER ALL
SPECIFICATION:
CURRENT RATING:1.8A FOR VBUS AND GND CONTACTS
1.5A FOR OTHER CONTACTS
WITHSTANDING VOLTAGE:100V AC(RMS)
INSULATION RESISTANCE:100MΩ MIN AT 100V DC
CONTACT RESISTANCE:30mΩ MAX FOR VBUS AND GND CONTACTS
50mΩ MAX FOR OTHER CONTACTS
MATING FORCE:3.57KgF MAX
UNMATING FORCE:1.02KgF MIN



11/10/27	VICKY		NEW—DGW		AO
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED		CnC Tech,LLC			
				TITLE: USB 9P A/F DIP 90 15U" RoHS 蓝色成品	
X.X ±0.25	X.X° ±3.0°	APPD:	PRODUCT NO: 1003—001—01000		
X.XX ±0.15	X.XX° ±1.00°	CHECK:	DATE	SCALE	PAGE
X.XXX ±0.05	X.XXX° ±0.500°	DRAW:	2011.10.27	FREE MM	CD 1