



Storage Rack for HIS-Boxes

• HIS-Service Station

This sturdy Service Station contains up to 5 dispensers. It can be put on a bench or mounted to a wall. A special cutter is included and makes it easy to cut the tubing length as desired

Technical Table	
Article-No.	Description
365-30100	HIS-Service Station incl. cutter, contents: 5 dispensers HIS-3 (shrink ratio: 3:1), black, sizes are as follows: HIS-3/1, HIS-6/2, HIS-12/4 (2 pcs.), HIS-24/8
365-20000	HIS-Service Station incl. cutter, contents: 5 dispensers HIS-Pack (shrink ratio: 2:1), black, sizes are as follows: HIS-1/8, HIS-3/16, HIS-1/4, HIS-3/8, HIS 1/2 and one RiteOn Starter Pack
300-30000	HIS-Service Station incl. cutter, empty



HIS-Service Station contains 5 dispensers and a special cutter.

• HIS-PACK

Features and Benefits

- E-beam Crosslinked Polyolefin, thin-wall and flexible
- Shrink ratio 2:1
- Available in colours: black, red, blue, transparent and yellow/green.
- 10 sizes from 1.2mm to 25.4mm
- Handy dispenser box including table with full range of applications

Application

- General purpose electrical insulation
- Protection against corrosion and mechanical abrasion



HIS-A.

Material Data	
Material	Polyolefin, cross-linked (POX)
Shrink Ratio	2:1
Longitudinal change after shrinkage	+/- 5%
Minimum Shrink Temperature	+100 °C
Operating Temperature	-55 °C to +125 °C
Insulation Class	E (VDE 0530)
Dielectric Strength	20kV/mm according to ASTM D2671
Flammability	UL224 VW-1 (except clear)



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.



Heat Shrinkable Tubing 2:1 on a Reel

• HIS-PACK

Technical Table

Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT)	Pack Cont. (m)	Colour
300-30120	HIS-PACK-1.2/0.6	1.2	0.6	0.40	10	Black (BK)
300-30122	HIS-PACK-1.2/0.6	1.2	0.6	0.40	10	Red (RD)
300-30123	HIS-PACK-1.2/0.6	1.2	0.6	0.40	10	Transparent (CL)
300-30126	HIS-PACK-1.2/0.6	1.2	0.6	0.40	10	Blue (BU)
300-30160	HIS-PACK-1.6/0.8	1.6	0.8	0.40	10	Black (BK)
300-30162	HIS-PACK-1.6/0.8	1.6	0.8	0.40	10	Red (RD)
300-30163	HIS-PACK-1.6/0.8	1.6	0.8	0.40	10	Transparent (CL)
300-30166	HIS-PACK-1.6/0.8	1.6	0.8	0.40	10	Blue (BU)
300-30240	HIS-PACK-2.4/1.2	2.4	1.2	0.50	10	Black (BK)
300-30242	HIS-PACK-2.4/1.2	2.4	1.2	0.50	10	Red (RD)
300-30243	HIS-PACK-2.4/1.2	2.4	1.2	0.50	10	Transparent (CL)
300-30246	HIS-PACK-2.4/1.2	2.4	1.2	0.50	10	Blue (BU)
300-30320	HIS-PACK-3.2/1.6	3.2	1.6	0.50	10	Black (BK)
300-30322	HIS-PACK-3.2/1.6	3.2	1.6	0.50	10	Red (RD)
300-30323	HIS-PACK-3.2/1.6	3.2	1.6	0.50	10	Transparent (CL)
300-30326	HIS-PACK-3.2/1.6	3.2	1.6	0.50	10	Blue (BU)
300-30327	HIS-PACK-3.2/1.6	3.2	1.6	0.50	10	Green-Yellow (GNYE)
300-30480	HIS-PACK-4.8/2.4	4.8	2.4	0.50	10	Black (BK)
300-30482	HIS-PACK-4.8/2.4	4.8	2.4	0.50	10	Red (RD)
300-30483	HIS-PACK-4.8/2.4	4.8	2.4	0.50	10	Transparent (CL)
300-30486	HIS-PACK-4.8/2.4	4.8	2.4	0.50	10	Blue (BU)
300-30487	HIS-PACK-4.8/2.4	4.8	2.4	0.50	10	Green-Yellow (GNYE)
300-30640	HIS-PACK-6.4/3.2	6.4	3.2	0.60	5	Black (BK)
300-30642	HIS-PACK-6.4/3.2	6.4	3.2	0.60	5	Red (RD)
300-30643	HIS-PACK-6.4/3.2	6.4	3.2	0.60	5	Transparent (CL)
300-30646	HIS-PACK-6.4/3.2	6.4	3.2	0.60	5	Blue (BU)
300-30647	HIS-PACK-6.4/3.2	6.4	3.2	0.60	5	Green-Yellow (GNYE)
300-30950	HIS-PACK-9.5/4.7	9.5	4.7	0.60	5	Black (BK)
300-30952	HIS-PACK-9.5/4.7	9.5	4.7	0.60	5	Red (RD)
300-30953	HIS-PACK-9.5/4.7	9.5	4.7	0.60	5	Transparent (CL)
300-30956	HIS-PACK-9.5/4.7	9.5	4.7	0.60	5	Blue (BU)
300-30957	HIS-PACK-9.5/4.7	9.5	4.7	0.60	5	Green-Yellow (GNYE)
300-31270	HIS-PACK-12.7/6.4	12.7	6.4	0.60	5	Black (BK)
300-31272	HIS-PACK-12.7/6.4	12.7	6.4	0.60	5	Red (RD)
300-31273	HIS-PACK-12.7/6.4	12.7	6.4	0.60	5	Transparent (CL)
300-31276	HIS-PACK-12.7/6.4	12.7	6.4	0.60	5	Blue (BU)
300-31277	HIS-PACK-12.7/6.4	12.7	6.4	0.60	5	Green-Yellow (GNYE)
300-31900	HIS-PACK-19.1/9.5	19.1	9.5	0.80	5	Black (BK)
300-31902	HIS-PACK-19.1/9.5	19.1	9.5	0.80	5	Red (RD)
300-31903	HIS-PACK-19.1/9.5	19.1	9.5	0.80	5	Transparent (CL)
300-31906	HIS-PACK-19.1/9.5	19.1	9.5	0.80	5	Blue (BU)
300-31907	HIS-PACK-19.1/9.5	19.1	9.5	0.80	5	Green-Yellow (GNYE)
300-32540	HIS-PACK-25.4/12.7	25.4	12.7	0.90	5	Black (BK)
300-32542	HIS-PACK-25.4/12.7	25.4	12.7	0.90	5	Red (RD)
300-32543	HIS-PACK-25.4/12.7	25.4	12.7	0.90	5	Transparent (CL)
300-32546	HIS-PACK-25.4/12.7	25.4	12.7	0.90	5	Blue (BU)
300-32547	HIS-PACK-25.4/12.7	25.4	12.7	0.90	5	Green-Yellow (GNYE)

All dimensions in mm. Subject to technical changes.