



D




C

B


A




MATING CONNECTOR INTERFACE



TYPICAL RECEPTACLE CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)



RECOMMENDED CUT OUT
FOR 1.52 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

2.13	.084	6.60	.260	-	-
1.57	.062	5.08	.200	29.21	1.150
1.52	.060	5.05	.199	19.94	.785
0.38	.015	3.68	.145	19.69	.775
0.25	.010	3.18	.125	16.21	.638
0.13	.005	2.67	.105	16.13	.635
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

770335-1		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES: ON + 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 1°0'		DR 11-4-93 K. WHITAKER CHK 11-4-93 R. SWING APPD 11-4-93 C. CASH APPD 11-4-93 C. CASH PRODUCT SPEC -	
MATERIAL NYLON, UL 94V-2 NATURAL		NAME RECEPTACLE, PANEL MOUNT, 4 CIRCUIT, .062 PIN AND SOCKET	
FINISH -		APPLICATION SPEC -	
WEIGHT -		SCALE 5:1	
CAGE CODE 00779		DRAWING NO C=770335	
SHEET 1 OF 1		CUSTOMER DRAWING	