



4

3




2

1


LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION		DATE	APVD
			A1	REVISED PER ECO-11-005301		6APR11	HMR



RECOMMENDED PCB LAYOUT



2 PIN



3 PIN

0.36g	17.50	19.30	20.50	15	1-1734829-5
0.34g	16.25	18.05	19.25	14	1-1734829-4
0.32g	15.00	16.80	18.00	13	1-1734829-3
0.30g	13.75	15.55	16.75	12	1-1734829-2
0.27g	12.50	14.30	15.50	11	1-1734829-1
0.26g	11.25	13.05	14.25	10	1-1734829-0
0.23g	10.00	11.80	13.00	09	1734829-9
0.21g	8.75	10.55	11.75	08	1734829-8
0.19g	7.50	9.30	10.50	07	1734829-7
0.16g	6.25	8.05	9.25	06	1734829-6
0.14g	5.00	6.80	8.00	05	1734829-5
0.12g	3.75	5.55	6.75	04	1734829-4
0.10g	2.50	4.30	5.50	03	1734829-3
0.08g	1.25	3.05	4.25	02	1734829-2
WEIGHT	C	B	A	NO. OF CONTACTS	PART NUMBER
			DIMENSIONS		

- NOTE:
- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
 - FINISH:
CONTACTS: 2.54μm [100μ"] MIN. MATTE-TIN OVER
1.27μm [50μ"] MIN. NICKEL ON ENTIRE CONTACT.
 - WAVE SOLDER CAPABLE TO 265°C PER **TE Connectivity** TEST SPEC. 109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5

1 PLC ± 0.38

2 PLC ± 0.25

3 PLC ± 0.15

4 PLC ± -

ANGLES ± -

FINISH

SEE NOTE

DWNH. HUANG31MAY2007

CHKS. HOU31MAY2007

APVDW.J. KE31MAY2007

PRODUCT SPEC

108-57499

QUALIFICATION TEST REPORT

501-57573

WEIGHTSEE TABLE

CUSTOMER DRAWING

TE Connectivity

NAME

1.25MM PITCH, WIRE TO BOARD CONNECTOR
HEADER, R/A, DIP TYPE

SIZEA3

CAGE CODE00779

DRAWING NOC-1734829


RESTRICTED TO

SCALE—


SHEET1 OF 2

REV A1

LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



5.95 Kg	2.18 Kg	30	200	6000 PCS	15
5.92 Kg	2.15 Kg	32		6400 PCS	14
5.92 Kg	2.15 Kg	34		6800 PCS	13
5.96 Kg	2.19 Kg	36		7200 PCS	12
5.87 Kg	2.10 Kg	39		7800 PCS	11
5.97 Kg	2.20 Kg	43		8600 PCS	10
5.97 Kg	2.20 Kg	47		9400 PCS	09
5.95 Kg	2.18 Kg	52		10400 PCS	08
5.97 Kg	2.21 Kg	58		11600 PCS	07
5.85 Kg	2.11 Kg	66		13200 PCS	06
5.93 Kg	2.16 Kg	76		15200 PCS	05
5.93 Kg	2.16 Kg	90		18000 PCS	04
5.95 Kg	2.18 Kg	110		22000 PCS	03
5.92 Kg	2.14 Kg	141		28200 PCS	02
GROSS WEIGHT	NET WEIGHT	PCS/TUBE	TUBES /CARTON	QUANTITY	NO. OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. HUANG 31MAY2007		TE Connectivity								
		CHK S. HOU 31MAY2007										
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME								
		APVD W.J. KE 31MAY2007		1.25MM PITCH, WIRE TO BOARD CONNECTOR HEADER, R/A, DIP TYPE								
		PRODUCT SPEC										
		—										
		APPLICATION SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO								
		—										
MATERIAL		FINISH		A300779		C=1734829	—					
				CUSTOMER DRAWING				SCALE	SHEET	2 OF 2	REV	A1
								—				