



# EPIC® Rectangular Connectors



HBE 24 Housings: Single Lever on Base

## HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C



**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 10121900     | 101219NP | 19121900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 10111900     | 101119NP | 19111900 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| Side Entry              | 21            | 3/4" | 25     | 10113900     | 101139NP | 19113900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 10123900     | 101239NP | 19123900 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Top Entry Metric hoods do not come with a neck.

## HIGH PROFILE HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 70144400     | 701444NP | 79144400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 70144600     | 701446NP | 79144600 | 53015160                                           | 52015760  | 53111040      | 53112040      |
|                         | -             | -    | 40     | -            | -        | 79144800 | -                                                  | -         | 53111050      | 53112050      |
| Side Entry              | 21            | 3/4" | 25     | 70154400     | 701544NP | 79154400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 70154600     | 701546NP | 79154600 | 53015160                                           | 52015760  | 53111040      | 53112040      |
|                         | -             | -    | 40     | -            | -        | 79154800 | -                                                  | -         | 53111050      | 53112050      |



High Profile Metric hoods do not come with a neck.

# EPIC® Rectangular Connectors



HBE 24 Housings: Single Lever on Base


## PANEL MOUNT BASES






**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C  
**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Description                    | Part Numbers |
|--------------------------------|--------------|
| Panel Mount without Dust Cover | 10102900     |
| Panel Mount with Dust Cover    | 10103900     |

All dimensions are in mm.



## SURFACE MOUNT BASES




All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| # of Entries            | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries               | 21            | 3/4" | 25     | 10105900     | 101059NP | 19105900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry                 | 21            | 3/4" | 25     | 10104900     | 101049NP | 19104900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 2 Entries w/ dust cover | 21            | 3/4" | 25     | 10109900     | 101099NP | 19109900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry with dust cover | 21            | 3/4" | 25     | 10107900     | 101079NP | 19107900 | 53015150                                           | 52015750  | 53111030      | 53112040      |

## DUST COVERS WITH ATTACHMENT STRING



**Material:** Thermoplastic Resin

**Temperature:** -40°C to 125°C




|                                                                                                     | Part #   |
|-----------------------------------------------------------------------------------------------------|----------|
| Dust cover with single lever for HBE 24 Hoods                                                       | 10118600 |
| Dust cover with single lever bolts for HBE 24 Panel Mount or Surface Mount Base/ Cable Coupler Hood | 10118700 |

# EPIC® Rectangular Connectors

HBE 24 Housings: Single Lever on Base



## HIGH PROFILE SURFACE MOUNT BASES



All dimensions are in mm.


**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated


| # of Entries              | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|---------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                           | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries                 | 21            | 3/4" | 25     | 70161200     | 701612NP | 79161200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                           | 29            | 1"   | 32     | 70161400     | 701614NP | 79161400 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| 1 Entry                   | 21            | 3/4" | 25     | 70160200     | 701602NP | 79160200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                           | 29            | 1"   | 32     | 70160400     | 701604NP | 79160400 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| 2 Entries with dust cover | 21            | 3/4" | 25     | 70165200     | 701652NP | 79165200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                           | 29            | 1"   | 32     | 70165400     | 701654NP | 79165400 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| 1 Entry with dust cover   | 21            | 3/4" | 25     | 70164200     | 701642NP | 79164200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                           | 29            | 1"   | 32     | 70164400     | 701644NP | 79164400 | 53015160                                           | 52015760  | 53111040      | 53112040      |

## CABLE COUPLER HOODS

### STANDARD PROFILE



### HIGH PROFILE



**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Profile          | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                  | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Standard Profile | 21            | 3/4" | 25     | 10127900     | 101279NP | 19127900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                  | 29            | 1"   | 32     | 10117900     | 101179NP | 19117900 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| High Profile     | 21            | 3/4" | 25     | 70142400     | 701424NP | 79142400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                  | 29            | 1"   | 32     | 70142600     | 701426NP | 79142600 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Cable coupler metric hoods do not come with a neck.



# EPIC® Rectangular Connectors



HBE 24 Housings: Double Levers on Base

## HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C



**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 101210C0     | 101210NP | 19121000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 101110C0     | 101110NP | 19111000 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| Side Entry              | 21            | 3/4" | 25     | 101130C0     | 101130NP | 19113000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 101230C0     | 101230NP | 19123000 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Top Entry metric hoods do not come with a neck.

## HIGH PROFILE HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.




**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 701504C0     | 701504NP | 79150400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 701506C0     | 701506NP | 79150600 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| Side Entry              | -             | -    | 40     | -            | -        | 79150800 | -                                                  | -         | 53111050      | 53112050      |
|                         | 21            | 3/4" | 25     | 701524C0     | 701524NP | 79152400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 701526C0     | 701526NP | 79152600 | 53015160                                           | 52015760  | 53111040      | 53112040      |
|                         | -             | -    | 40     | -            | -        | 79152800 | -                                                  | -         | 53111050      | 53112050      |

High Profile Metric hoods do not come with a neck.

### PANEL MOUNT BASES






All dimensions are in mm.

**Specifications:**  
**Temperature Range:**  
**Protection class:**  
**Material:**

DIN 43652  
 -40°C to +125°C  
 NEMA 4, NEMA 12, IP65  
 Aluminum alloy, powder coated

| Description                    | Part Numbers |
|--------------------------------|--------------|
| Panel Mount without Dust Cover | 101020C0     |

### SURFACE MOUNT BASES



All dimensions are in mm.

**Specifications:**  
**Temperature Range:**

DIN 43652  
 -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| # of Entries | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|--------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|              | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries    | 21            | 3/4" | 25     | 101050C0     | 101050NP | 19105000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry      | 21            | 3/4" | 25     | 101040C0     | 101040NP | 19104000 | 53015150                                           | 52015720  | 53111030      | 53112030      |

### DUST COVERS WITH ATTACHMENT STRING



**Material:** Thermoplastic Resin

**Temperature:** -40°C to +125°C



|                                                                                                        | Part #   |
|--------------------------------------------------------------------------------------------------------|----------|
| Dust cover with double levers and gasket for HBE 16 Hoods                                              | 10119500 |
| Dust cover with double lever bolts for HBE 16 Panel Mount or Surface Mount Base/<br>Cable Coupler Hood | 10118000 |

# EPIC® Rectangular Connectors



HBE 24 Housings: Double Levers on Base

## HIGH PROFILE SURFACE MOUNT BASES



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C



**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| # of Entries               | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|----------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                            | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries without cover    | 21            | 3/4" | 25     | 70136200     | 701362NP | 79136200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                            | 29            | 1    | 32     | 701364C0     | 701364NP | 79136400 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| 1 Entry without dust cover | 21            | 3/4" | 25     | 701352C0     | 701352NP | 79135200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                            | 29            | 1"   | 32     | 701354C0     | 701354NP | 79135400 | 53015160                                           | 52015760  | 53111040      | 53112040      |

## CABLE COUPLER HOODS

### STANDARD PROFILE

### HIGH PROFILE



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Profile          | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                  | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Standard Profile | 21            | 3/4" | 25     | 101270C0     | 101270NP | 19127000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                  | 29            | 1    | 32     | 101170C0     | 101170NP | 19117000 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| High Profile     | 21            | 3/4" | 25     | 701404C0     | 701404NP | 79140400 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                  | 29            | 1"   | 32     | 701406C0     | 701406NP | 79140600 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Metric hoods do not come with a neck.