



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ PKNI 10 B

PKNI 10 B

datasheet for PKNI 10 B
article number: 930136101



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 136-101
description:	Pole terminal with claw edge, captive insulated head and insulated ring. 6 mm diameter nickel-plated brass threaded bolt with 2.6 mm diameter transverse hole. For insulated non-rotating installation in equipment chassis and switch panels up to 3.5 mm wall
typ:	PKNI 10 B rot / red
system:	4mm system
order number:	930 136-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	4 mm socket (unsprung), 2.6 mm cross hole
type of termination:	M6 thread, solder
rated voltage:	30 VAC / 60 VDC
rated current:	63 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	
	