

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0908163010

Status:

Active

Overview:

Picoflex Ribbon-Cable Connectors

Description:

Picoflex Surface Mount Latched Vertical Header with PCB Pegs, 10 Circuits, PdNi with Gold Flash Plating, Black

Documents:

3D Model

3D Model (PDF)


Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	90816
Application	Signal, Wire-to-Board
Overview	Picoflex Ribbon-Cable Connectors
Product Name	Picoflex
UPC	883906499280
Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	5
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Nickel
Material - Resin	Nylon
Net Weight	0.480/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	1.05mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

Material Info



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90816 Series

Mates With

90327 Picoflex PF-50

This document was generated on 08/18/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION