





THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ——— 2 LB MAX	CONTACT ARRANGEMENT S P D T
RELEASE FORCE ————— 1/2 LB	
DIFFERENTIAL TRAVEL ——— .004 MAX	
OVERTRAVEL ————— .219 MIN	
BASIC SWITCH REPLACEMENT B2-2R708-P7	-L96- 15 A-125, <u>250</u> , OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC; 1/4 HP- <u>250</u> VAC  

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT .500 LB

NOTE

1 - 8-32 UNC X (.219) BINDER HEAD,COMBINATION , TERMINAL SCREWS
AND CUPWASHERS (SEMS)(3)