

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


82-26-4417

Status:

Active

Description:

2.00mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 34) Stranded, Topcoat, 17 Circuits, Reel 30.48m Length



Series

image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	24462
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800754989886

Physical

Cable Length	30.48m
Circuits (Loaded)	17
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	2.00mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	26
Wire/Cable Type	(7x34) Stranded, Topcoat

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	24462-17-100B
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-24462-001
---------------	--------------

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

24462Series

Use With

52484 Wire-to-Board, IDT Receptacle Housing

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION