



Tie Harness Mounts are designed to be attached to the wire harness during assembly with 2 cable ties. Ties can be installed by hand or more efficiently with *PANDUIT* Automatic Cable Tie Tooling. Use with Harness Board Standoff Posts. Available with or without corrugated tubing location tab.

Part Number: THMSP20F-C30

Product Family: Tie Harness Mounts

Product Line: Push/Tree Barb

RoHS Compliancy Status: Compliant

Part Description: Harness Cable Tie Mount

Product Type: Cable Tie Mounts - Tie Harness Mount

Material: Heat Stabilized Nylon 6.6

Color: Black

UL Recognized: E136577

Height (In.): .47

Height (mm): 16.5

Length (In.): 1.54

Length (mm): 39.1

Width (In.): .37

Width (mm): 9.4

Corrugated Tubing Tab: No

Environment: Indoors/High Temp

Flammability Rating: UL94 V-2

Max. Panel Thickness (In.): .160

Max. Panel Thickness (mm): 4.1

Mounting Method: Push Barb

