

- Replacement for 25 W E14 candle lamp
- 84% energy saving
- Lifetime of 25,000 hrs
- Ideal for general and decorative lighting at home and in hospitality environments. This candle lamp enhances the appeal of the chandelier and other luminaires both when lit up and when not.



Order Code 52123

General Data

Lamp Socket	E14
Design	Clear

Geometric Data

Length (mm)	100
Diameter (mm)	36
Weight (g)	40

Electric Data


Wattage (W)	4.0
Voltage (V)	220-240
Power Factor	≥ 0.90
Operating Frequency (Hz)	50-60


Photometric Data

Luminous Flux (lm)	250
CRI	≥ 80
CCT (K)	2700
Luminous Intensity (cd)	-
Beam Angle (°)	-
Lifetime (hrs)	25,000

Switching cycle	40,000
------------------------	--------

Wattage Equivalent (W)	25
-------------------------------	----





Order Code 52123

Product Description LED CLASSIC B 4.0W 2700K WW 250LM Blister

Technical Packaging Details

Barcode	023942521235
EAN 128	(02)00023942521235(37)04(91)14
EAN 14	50023942521230
Pack Dimensions (HxWxL)	198 mm x 118 mm x 45 mm
Pack Weight	58 g
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	208 mm x 90 mm x 248 mm
Cartons/Layer	144
Layers/Pallet	4
Units/Pallet	576

Photometric Diagram

52123

