



Heyco® Nylon Cable Ties

Regular Nyties®

Regular Nyties

- Smooth, radiused edges ensure that Nyties won't cut into the cable's insulation—or the installer's hand.
- One-piece design reduces cost and installation time.
- Nyties feature a bent tip for ease of pickup and insertion around small bundles. V-shaped raised ridges on the tip provide a sure grip.
- Close, evenly spaced teeth permit fine adjustment—from .025" (0,6 mm) on the smallest Nyties to .063" (1,6 mm) on the largest.

Screw Mountable Nyties

- Molded-in screw hole mount provides one-piece mounting and bundling.
- Mounting screws not included.

Push Mountable Nyties

- Snap quickly into holes with only fingertip pressure.
- Provide one-piece mounting and bundling.
- Hold securely in panels up to 1/8" (3,2 mm) thick.



PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS							
Min. Tensile Strength lbs.	N	Max. Bundle Diameter in.	mm.	Natural	UV Black		A Length		B Width		C Thickness		Min Bundle Diameter	
							in.	mm.	in.	mm.	in.	mm.	in.	mm.

Regular Nyties®

18	80	.75 1.50 2.00	19,1 38,1 50,8	3500 3503 3506	3502 3504 3507	NT 70 NT 70L NT 70E	3.80 6.25 8.00	97 159 203	.09	2,3	.045 1,1		.062	1,6
30	133	1.00	25,4	3510	3511	NT 90	5.20	132	.12	2,9				
40	178	1.25 2.00	31,8 50,8	3515 3850	3516 3851	NT 120 NT 170	6.20 8.25	158 210	.14	3,4	.050 1,3			
50	222	1.75 3.00	44,4 76,2	3520 3525	3521 3526	NT 150 NT 250	7.50 11.25	191 286	.19	4,8	.055 1,4			


Screw Mountable Nyties®

30	40	50	133	178	222	1.00	1.25	1.75	25,4	31,8	44,4	3550	3555	3560	-	-	-	MNT 90	MNT 120	MNT 150	5.50	6.20	7.50	140	158	191	.115	.135	.190	2,9	3,4	4,8	.045	.050	.055	1,1	1,3	1,4	4	8	10
----	----	----	-----	-----	-----	------	------	------	------	------	------	------	------	------	---	---	---	--------	---------	---------	------	------	------	-----	-----	-----	------	------	------	-----	-----	-----	------	------	------	-----	-----	-----	---	---	----



Push Mountable Nyties®

40	50	180	222	1.42	1.75	36,0	44,4	3907*	3904	-	-	PWMS-155 HSB	PMT 150	6.23	8.00	158	203	.14	.19	3,5	4,8	.047	.055	1,2	1,4	.19	.25	4,6	6,4
----	----	-----	-----	------	------	------	------	-------	------	---	---	--------------	---------	------	------	-----	-----	-----	-----	-----	-----	------	------	-----	-----	-----	-----	-----	-----


Standard color natural.
*PN 3907 color is black.



Regular Nyties



Screw Mountable Nyties



Push Mountable Nyties



Quick Specs

Material
Certifications

Flammability Rating
Temperature Rating

Nylon 6/6
Recognized under the Component Program of Underwriters' Laboratories File E54523
94V-2
185°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3610](#) [3605](#)