

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
DF	X5	A		RELEASED PER ECO-05-001646	06-05	AA

PART NO.	'A'	'B'
5830637-5	36.00 [914.4]	.38 [9.7]
5830637-8	47.25 [1200.1]	.50 [12.7]
1-5830637-2	12.00 [304.8]	.38 [9.7]
1-5830637-3	18.00 [457.2]	.38 [9.7]
2-5830637-3	17.00 [431.8]	.50 [12.7]
2-5830637-4	48.00 [1219.2]	.38 [9.7]
2-5830637-8	24.00 [609.6]	.38 [9.7]
3-5830637-6	118.00 [2997.2]	.38 [9.7]

1. TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ± 1.2 [± 3.0]
24 INCHES [609.6] & UP = $\pm 1\%$
2. MARKED PER MIL-STD-130.
3. INSULATION CUT TO LENGTH 'B' BUT NOT REMOVED.
4. TO MATE WITH AMP LGH-1L
RECEPTACLE WITH 1.69 [42.93] BARREL DEPTH.
5. OPERATING VOLTAGE: 25 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
6. MIN LEAD LENGTH IS 5.00 [127.0].

