

Fully rotational, swivel vice made from cast iron with black crackle finish. Lockable in any position by rear lever.

SPECIFICATIONS

Jaw Width:	60mm
Jaw Opening:	45mm
'G' Clamp Opening:	75mm
Height:	182mm
Length:	150-195mm
Width:	65mm
Weight:	2.3kg



Moulded glass filled polyamide, and steel jaw linings for the aluminium vice *CAT.NO. 606*.

The moulded linings are available as plain smooth-faced or serrated and have vertical, horizontal and in the case of the smooth-faced jaws, diagonal 'V' slots.

All jaws supplied in pairs.

Moulded serrated *CAT.NO. 60601*

Moulded plain *CAT.NO. 60602*

Steel *CAT.NO. 60603*

Robust, lightweight, medium duty vice made from high-quality diecast aluminium alloy, finished in black epoxy resin. May be mounted directly onto a bench, or in a 'G'-Clamp, thus turning it into a fully rotational swivel vice. May also be mounted on either of the swivel ball joint bases which allows complete freedom of movement around a 180° sphere.

Vice comes supplied with a pair of hardened and ground steel jaws, soft jaws optional.

SPECIFICATIONS


Jaw Width:	50mm
Jaw Opening:	80mm
Height:	80mm
Length:	200mm
Width:	55mm
Weight:	700gms

Aluminium vice direct bench mount *CAT.NO. 606*


Aluminium vice and 'G'-Clamp *CAT.NO. 60604*

Aluminium vice and swivel ball joint, bench mounting base *CAT.NO. 60605*


Aluminium vice and 'G'-Clamp, swivel ball joint base *CAT.NO. 60606*



MEDIUM DUTY VICE



LIGHTWEIGHT ALUMINIUM VICE



JAW LININGS