



data sheet

system:	Lithium-Ion-Battery
nominal voltage:	3,7V
end charge voltage:	4,2V
max. charge current:	800mA
charge conditions	
standard charge:	400mA for 3,5h min.
fast charge:	800mA for 2,5h min.
charging method:	CC-CV (constant current and constant voltage)
capacity	after standard charge
nominal:	800mAh at 0,2C discharge to 2,75V
minimal:	720mAh at 0,2C discharge 680mAh at 1C discharge
max. discharge current:	800mA
life time expectancy:	> 300 cycles
ambient temperature range	
charge:	0...45°C
discharge:	-20...60°C
long term storage:	-20...35°C (less than 1 year)
weight:	approx. 29g
dimensions:	L1: 30,4mm L2: 12,5mm L3: 37,2mm



49

	specifications for model/type:	A-PAN CGA-S007
	Ansmann drawing number / part number:	5022963
	drawn by / date:	SVK/07.04.2008